

## SNCA-ZX104

Hybrid camera receiver allows seamless integration of analogue and IP



### Overview

The SNCA-ZX104 Hybrid Camera Receiver allows customers to seamlessly integrate images from four different hybrid cameras, enabling their easy and cost-effective migration towards HD IP video surveillance systems.

The SNCA-ZX104 4 channel receiver offers 4 x BNC camera input and 4 x BNC analogue video output.

### Specifications

#### Camera Connection

Number of Cameras Supported 4

Supported Serial PTZ Control Protocol Pelco-D

#### System Requirements

Operating System Microsoft Windows XP (32 bit)  
Windows Vista (32 bit)  
Windows 7 (32 bit/64 bit)

Web Browser	Microsoft Internet Explorer Ver. 6.0, Ver. 7.0, Ver. 8.0
-------------	---

## Interface

Analogue Video Output	BNC x4 (1.0 Vp-p, 75 $\Omega$ , NTSC or PAL)
-----------------------	--

SLOC Port	BNC x4 (75 $\Omega$ )
-----------	-----------------------

Network Port	10BASE-T/100BASE-TX (RJ-45)
--------------	-----------------------------

Serial Interface	RS-485 x1 (I/O port for PTZ camera control)
------------------	---

## General

Power Requirements	DC 12 V (AC 100 V to AC 240 V, 50/60 Hz for AC adaptor)
--------------------	---

Power Consumption	Approx. 12.0 W, Approx. 0.22 A/0.12 A (AC adaptor, AC 100 V to AC 240 V)
-------------------	--

Operating Temperature	0°C to +45°C +32°F to 113°F
-----------------------	--------------------------------

Storage Temperature	-20°C to +60°C -4°F to +140°F
---------------------	----------------------------------

Operating Humidity	20% to 80% (no condensation)
--------------------	------------------------------

Storage Humidity	20% to 80% (no condensation)
Dimensions (W x H x D) *1	210 mm x 44 mm x 250 mm (without projecting parts) 8 3/8 inches x 1 3/4 inches x 9 7/8 inches (without projecting parts)
Mass	Approx. 1.1 kg Approx. 2 lb 7 oz
Supplied Accessories	CD-ROM (User's Guide, and supplied programs) (1) Installation Manual (1) B&P warranty booklet (1) AC adaptor (1) Power code I/O port connector (1)

## Notes

Notes

[\*1] The values for dimensions are approximate.

## Related products



### SCA-M30

High quality, ceiling microphone for IP security cameras.



### SCA-S30



### UNI-OPL7C3

Outdoor Pressurized dome camera housing



### SNCA-HRX550/EXT12V

Robust, IP66 rated dome housing for



## **SNCA- HRX550EXT/W**

Outdoor wireless  
dome camera housing

## Gallery

