

VPL-FHZ91L

9,000 lm (9,800 lm center) laser light source projector (colour availability may vary by country)



Overview

Combining spectacular image quality with easy set-up and minimal maintenance needs, these high-brightness 3LCD laser projectors are ideal for installation in larger spaces.

Captivate your audience in conference halls, lecture theatres, galleries, museums, visitor attractions and other large spaces. A high light output of 9,000 lumens ensures big-screen presentations with extra presence, even in brightly lit rooms.

Impressive picture quality is boosted by Sony's unique super resolution Reality Creation technology. This uses a powerful pattern-matching database to optimise lower-resolution images, enhancing clarity without increasing digital picture noise.

Save time with Sony's Intelligent Setting function that simplifies installation with pre-sets to optimise brightness, cooling, colour and other projector settings. You'll be rewarded with great pictures in every environment.

You'll appreciate an industry-leading lens shift adjustment range and a wide choice of interchangeable lenses, giving more options to install the projector in any space, including classrooms and halls with high ceilings. For extra flexibility the VPLL-Z4107 short throw lens is ideal when positioning the projector close to the screen to avoid ceiling-mounted obstructions.

Features

Reduced maintenance

The laser light source offers up to 20,000 hours* operation without lamp exchange, reducing maintenance needs compared with traditional projectors.

** Depending on usage environment.*

Consistent brightness

Experience consistent image brightness throughout the laser light source's 20,000 hours recommended lifespan.

Networked control and monitoring

Ideal for integration in AV environments with leading control, monitoring and management systems such as Crestron Connected™ and Extron® XTP™ Systems.*

** Extron and XTP Systems are trademarks of RGB Systems Inc.*

Easy edge blending

Seamlessly join colour-matched images from multiple projectors for stunning super-size displays in corporate and education environments.

Versatile lens options

There's a wide range of lens options to suit virtually any size of room and throw requirements. Quick-release bayonet mount simplifies lens exchange.

Generous lens shift range

Enjoy greater flexibility to position the projector in restricted spaces, ensuring that audience and presenters aren't distracted by the light source.

Lens position memory

Memorise and recall up to six settings for projected image size, position and aspect ratio, saving time in different environments.

(Requires optional VPLL-Z4111 lens)

Stylish blend-in design

The slim, stylish body features a flat top surface that blends discreetly into any space when the projector is ceiling mounted.

Specifications

Display system

| | |
|----------------|--------------|
| Display system | 3 LCD system |
|----------------|--------------|

Display device

| | |
|--------------------------------|---|
| Size of effective display area | 1" x 3 BrightEra LCD Panel, Aspect ratio: 16:10 |
|--------------------------------|---|

| | |
|------------------|------------------------------------|
| Number of pixels | 6,912,000 (1920 x 1200 x 3) pixels |
|------------------|------------------------------------|

| | |
|--------------|-------|
| Aspect ratio | 16:10 |
|--------------|-------|

| | |
|------------|----------------------------|
| Resolution | WUXGA (1920 x 1200 pixels) |
|------------|----------------------------|

Projection lens

| | |
|-------|--------------------------------|
| Focus | Powered/Manual(Depend on lens) |
|-------|--------------------------------|

| | |
|-----------------------|--------------------------------|
| Zoom - Powered/Manual | Powered/Manual(Depend on lens) |
|-----------------------|--------------------------------|

| | |
|--------------|----------------|
| Zoom - Ratio | Depend on Lens |
|--------------|----------------|

| | |
|-------------|----------------|
| Throw ratio | Depend on Lens |
|-------------|----------------|

| | |
|--------------------------------|---------|
| Lens shift - Powered/Manual | Powered |
|--------------------------------|---------|

| | |
|---|--|
| Lens shift - Range Vertical/Horizontal | Range Vertical: Depend on Lens Range Horizontal: Depend on Lens |
|---|--|

Light source

| | |
|------|-------------|
| Type | Laser diode |
|------|-------------|

Filter replacement cycle (Max.)

| | |
|------------------------------------|--------------------------------|
| Filter replacement cycle (Max.) | 10,000 H (service maintenance) |
|------------------------------------|--------------------------------|

Screen size

| | |
|-------------|----------------|
| Screen size | Depend on Lens |
|-------------|----------------|

Light output *1

| | |
|----------------|---------------------------------|
| Mode: Standard | 9,000lm *2 / 9,800lm (Center)*3 |
|----------------|---------------------------------|

| | |
|--------------|---------|
| Mode: Middle | 8,000lm |
|--------------|---------|

| | |
|-----------|---------|
| Mode: Low | 7,000lm |
|-----------|---------|

Colour light output *1

| | |
|----------------|---------|
| Mode: Standard | 9,000lm |
|----------------|---------|

| | |
|--------------|---------|
| Mode: Middle | 8,000lm |
|--------------|---------|

| | |
|-----------|---------|
| Mode: Low | 7,000lm |
|-----------|---------|

Contrast ratio *1

| | |
|--|--|
| Contrast ratio (full white / full black) | Contrast ratio (full white / full black) : ∞ : 1 |
|--|--|

Displayable scanning frequency

| | |
|------------|------------------|
| Horizontal | 15 kHz to 92 kHz |
|------------|------------------|

| | |
|----------|----------------|
| Vertical | 48 Hz to 92 Hz |
|----------|----------------|

Accepted signal resolution

| | |
|-----------------------|--|
| Computer signal input | Maximum signal resolution: 1920 x 1200 |
|-----------------------|--|

| | |
|--------------------|--|
| Video signal input | 480/60i, 576/50i, 480/60p, 576/50p, 720/60p, 720/50p, 1080/60i, 1080/50i The following items are available for digital signal only; 1080/60P, 1080/50p, 1080/24p, 1080/30p *4 |
|--------------------|--|

Keystone correction (Max.)

| | |
|------------|----------------|
| Horizontal | +/- 30 degrees |
| Vertical | +/- 30 degrees |

INPUT OUTPUT (Computer/Video/Control)

| | |
|----------|---|
| INPUT A | RGB / Y PB PR input connector: 5 BNC (female) |
| INPUT B | RGB input connector: Mini D-sub 15-pin (female) |
| INPUT C | DVI input connector: DVI-D 24-pin (single link), HDCP support HDCP: v1.4 |
| INPUT D | HDMI input connector: HDMI 19-pin, HDCP support HDCP: v1.4 |
| INPUT E | HDBaseT interface connector: RJ45, 3 play |
| INPUT F | Optional adaptor slot for 3G-SDI Input Adaptor (BKM-PJ20) |
| INPUT G | HTML Viewer |
| OUTPUT 1 | Monitor output for Input A/Input B |

| | |
|--------|---------------------------------------|
| | Connector: Mini D-sub 15-pin (female) |
| USB-1 | Type-A x 1 |
| USB-2 | Type-B x 1 (for service) |
| REMOTE | D-sub9pin male/RS232C |
| LAN | RJ45, 10BASE-T/100BASE-TX/1000BASE-T |

Acoustic Noise *1

Light output mode:
Standard 39dB

Light output mode:
Middle 39dB

Operating temperature / Operating humidity

Operating temperature /
Operating humidity 0°C to 45°C (32°F to 109°F) / 20% to 80% (no condensation)

Storage temperature / Storage humidity

Storage temperature / -10°C to +60°C (14°F to +140°F) /

Storage humidity 20% to 80% (no condensation)

Power requirements

| | |
|--------------------|--|
| Power requirements | AC 100 V to 240 V, 8.4 A to 3.4 A, 50 Hz / 60 Hz |
|--------------------|--|

Power consumption

| | |
|-------------------|-------|
| AC 100 V to 120 V | 840 W |
|-------------------|-------|

| | |
|-------------------|-------|
| AC 220 V to 240 V | 814 W |
|-------------------|-------|

Power Consumption (Standby Mode)

| | |
|-------------------|---|
| AC 100 V to 120 V | 0.50W (when "Standby mode" is set to "Low") |
|-------------------|---|

| | |
|-------------------|---|
| AC 220 V to 240 V | 0.50W (when "Standby mode" is set to "Low") |
|-------------------|---|

Power Consumption (Networked Standby Mode)

| | |
|-------------------|--|
| | 21.6W (LAN) |
| | 26.5W (HDBT) |
| AC 100 V to 120 V | 26.6W (ALL Terminals and Networks Connected, when "Standby Mode" is set to "Standard") |

| | |
|-------------------|--|
| | 21.3W (LAN) |
| | 26.5W (HDBT) |
| AC 220 V to 240 V | 26.6W (ALL Terminals and Networks Connected, when "Standby Mode" is set to "Standard") |

Standby Mode / Networked Standby Mode Activated

| | |
|---|-------------------|
| Standby Mode / Networked Standby Mode Activated | Approx. 2 Minutes |
|---|-------------------|

Heat dissipation

| | |
|-------------------|------------|
| AC 100 V to 120 V | 2866 BTU/h |
|-------------------|------------|

| | |
|-------------------|------------|
| AC 220 V to 240 V | 2777 BTU/h |
|-------------------|------------|

Dimensions (W x H x D) (without protrusions)

| | |
|--|--|
| Dimensions (W x H x D) (without protrusions) | Approx. 544 x 205 x 564 mm (21 13/32 x 8 1/16 x 22 7/32 inches) |
|--|--|

Mass

| | |
|------|-----------------------|
| Mass | Approx. 26 kg (58 lb) |
|------|-----------------------|

Supplied accessories

Remote commander RM-PJ30

Projection Lens

Projection Lens VPLL-Z4107, 4008, Z4111, Z4015,
Z4019, Z4025, Z4045

Optional Projection Lens

VPLL-Z4107 Throw Ratio: 0:75:1 to 0:94:1
Lens Shift - Range Vertical: +/-50%
Lens Shift - Range Horizontal:
+/-24%

VPLL-4008 Throw Ratio: 1:00:1
Lens Shift - Range Vertical: +/-32%
Lens Shift - Range Horizontal:
+/-15%

VPLL-Z4111 Throw Ratio: 1:30:1 to 1:96:1
Lens Shift - Range Vertical: +/-99%
Lens Shift - Range Horizontal:
+/-51%

VPLL-Z4015 Throw Ratio: 1:85:1 to 2:44:1
Lens Shift - Range Vertical: +/-98%
Lens Shift - Range Horizontal:
+/-51%

| | |
|------------|---|
| VPLL-Z4019 | <p>Throw Ratio: 2:41:1 to 3:07:1</p> <p>Lens Shift - Range Vertical: +/-107%</p> <p>Lens Shift - Range Horizontal: +/-57%</p> |
| VPLL-Z4025 | <p>Throw Ratio: 3:02:1 to 5:58:1</p> <p>Lens Shift - Range Vertical: +/-107%</p> <p>Lens Shift - Range Horizontal: +/-57%</p> |
| VPLL-Z4045 | <p>Throw Ratio: 5.56:1 to 7.5:1</p> <p>Lens Shift - Range Vertical: +/-107%</p> <p>Lens Shift - Range Horizontal: +/-57%</p> |

Notes

| | |
|----|---|
| *1 | <p>The figures are approximate. They vary depending on the environment or how the projector is used.</p> |
| *2 | <p>The value is in accordance with ISO 21118, and may differ depending on the actual unit. Brightness and contrast vary</p> |

depending on use conditions and environments.

*3

The value is light output measured at center area of screen in Standard mode, and average of all products shipped.

*4

When using BKM-PJ20

Gallery

