

## WD-850

### UHF Antenna Divider



#### Overview

- Provides diversity output for up to four receivers/tuner base units
- Power supplied to the Sony UHF antenna
- Cascade output can be used for an additional antenna-divider or receiver/tuner base unit
- Two pair of antenna input connectors to expand the operating area of a wireless microphone system

#### Specifications

##### Group heading

Frequency range      US : 470 to 806 MHz  
                                 CE : 470 to 862 MHz  
                                 J : 770 to 810 MHz

---

Channel distribution    Inputs: 2 pairs Outputs: 4 pairs

---

Antenna Input/Output   BNC-R, 50 ohms

---

Cascade output         1 pair

---

Power supply for  
antenna booster

---

(supplied from antenna input connectors)	DC 9 V/OFF switchable
Power requirements	US: 120 V AC, 60 Hz CE: 230 V, 50 Hz J: AC 100V, 50Hz/60Hz
Power consumption	18 W (when 100mA is being supplied to the antenna booster)
Dimensions (W x H x D)	Approx. 482 × 44 × 285 mm (19 x 1 3/4 x 11 1/4 inches)
Mass	Approx. 4.4 kg (9 lb 11 oz)

## Supplied Accessories

Audio output connector	50 ohms terminator (6) AC power cord (1) Operating Instructions (1)
------------------------	---

## Related products



### **DWR-R03D**

DWX Series 2-channel digital wireless receiver

## Gallery

