

## VPL-FW65

6,300 lumens WXGA 3LCD  
installation projector (colour  
availability may vary by country)



### Overview

#### **Bring presentations to life with impressive brightness, flexible integration and powerful picture features.**

The VPL-FW65 installation projector is ideal for a wide range of business, education and entertainment applications. The energy-efficient High Pressure Mercury (HPM) lamp source is teamed with Sony's advanced BrightEra 3LCD projection engine to deliver extremely bright, crisp WXGA resolution images with powerful 6300 lumens maximum light output and rich, stable colours. Reality Creation and Contrast Enhancer technologies fine-tune image quality even further to assure exceptional clarity and realism with every presentation.

Offering a stylish blend-in design, tidy cable management and low fan noise, the VPL-FW65 fits smoothly into almost any environment – from academic institutions, corporate, medical training and public sector organisations to visitor attractions and retail spaces. Seamlessly blend images from multiple projectors to create super-sized displays, or project accurately proportioned images onto angled or curved surfaces. Mount the projector at any angle, even on its side or upside down. Set-up is easy with a friendly installation menu.

## Features

### **Very high image quality with BrightEra 3LCD projection engine**

The energy-efficient High Pressure Mercury (HPM) lamp source is coupled with Sony's acclaimed BrightEra 3LCD projection engine to ensure very high 6300 lumen image brightness with vivid, natural colour reproduction.

### **Advanced picture refinement technologies**

Picture quality is boosted by advanced processing featured on Sony home cinema projectors. Reality Creation uses a powerful pattern-matching database to optimise every pixel. Contrast Enhancer actively analyses and refines dark and light image areas for sparkling highlights and rich, deep blacks.

### **Crisp WXGA image quality**

View PC presentations or videos with WXGA (1280 x 800) 16:10 resolution.

### **Hassle-free automatic filter cleaning**

Focus on great-looking images instead of arduous maintenance tasks: automated filter cleaning system removes dust every 100 hours.

### **Powered Wide Lens Shift**

Generous lens shift adjustments give more flexibility for positioning the projector where you need it: close to ceilings or even horizontally offset.

### **Included powered standard zoom lens plus wide choice of lens options**

Installation flexibility is increased by a wide range of compatible lens options to suit virtually any size of room and throw requirements. Quick-release bayonet mount simplifies quick lens exchange.

### **Supports HDBaseT**

Simpler, more cost-effective installation and connectivity with

digital transmission of HD video, audio and networking/control over a single Ethernet cable.

### **Create super-size displays with Edge Blending**

Seamlessly join accurately colour-matched images from multiple projectors, simplifying creation of stunning super-size displays for corporate and education.

### **Project onto non-flat surfaces with Image Warping**

Easily correct image geometry for natural-looking projections – even on convex or concave surfaces. Corner and edge correction can be easily adjusted with the supplied remote and on-screen menu.

### **Quiet operation**

Low fan noise ensures discreet, unobtrusive operation in quiet environments from museums and galleries to lecture

### **Slim, attractive blend-in design**

The slim, stylish case design features a flat top surface that blends in discreetly when the projector is ceiling mounted. The clean appearance is accentuated by a terminal cover that reduces cable clutter.

### **Picture Mode**

Picture Mode ensures great-looking presentations in a wide range of operating conditions. Select Standard, Dynamic, Brightness Priority or Multi Screen mode for optimised image quality, with any source and in every room.

### **Simple set-up with friendly Installation menu**

Easily adjust projector settings with remote commander, including image warping and edge blending.

### **Project Side by Side**

Project images from two inputs at the same time: ideal for applications such as video conferencing and medical training

where two images need to be seen simultaneously.

## Specifications

### Display system

Display system	3 LCD system
----------------	--------------

### Display device

Size of effective display area	0.76" (19 mm) x 3 BrightEra LCD Panel, Aspect ratio: 16:10
--------------------------------	--

Number of pixels	3,072,000 (1280 x 800 x 3) pixels
------------------	-----------------------------------

### Projection lens \*1

Focus	Powered
-------	---------

Zoom - Powered/Manual	Powered (Approx. 1.6 x)
-----------------------	-------------------------

Throw ratio	1.39:1 to 2.23:1
-------------	------------------

Lens shift - Powered/Manual	Powered
-----------------------------	---------

Lens shift - Range Vertical	-5.0%, +60%
-----------------------------	-------------

Lens shift - Range Horizontal	+/- 32%
-------------------------------	---------

## Light source

Type	Ultra high pressure mercury lamp
------	----------------------------------

Wattage	370 W type
---------	------------

## Recommended lamp replacement time \*2

Lamp mode: High	3000 H
-----------------	--------

Lamp mode: Low	4000 H
----------------	--------

## Filter cleaning / replacement cycle (Max.)\*2

Filter cleaning / replacement cycle (Max.)	20000 H (service maintenance)
--	-------------------------------

## Screen size

Screen size	40" to 600" (1.02 m to 15.24 m) (measured diagonally)
-------------	--

## Light output

Lamp mode: High	6300 lm
-----------------	---------

Lamp mode: Standard	4780 lm
---------------------	---------

## Color Light output

Lamp mode: High      6300 lm

Lamp mode: Standard   4780 lm

## Contrast ratio (full white / full black) \*3

Contrast ratio (full white / full black)      2000:1

## Displayable scanning frequency

Horizontal      15 kHz to 92 kHz

Vertical      48 Hz to 92 Hz

## Display resolution

Computer signal input      Maximum display resolution: 1920 x 1200 dots \*4

Video signal input      NTSC, PAL, SECAM, 480/60i, 576/50i, 480/60p, 576/50p, 720/60p, 720/50p, 1080/60i, 1080/50i  
The following items are available for digital signal (HDMI input) only; 1080/60P, 1080/50p, 1080/24p

## Color system

Color system	NTSC3.58, PAL, SECAM, NTSC4.43, PAL-M, PAL-N, PAL60
--------------	---

## Keystone correction (Max.)

Horizontal	+/- 30 degrees
------------	----------------

Vertical	+/- 30 degrees
----------	----------------

## OSD language

OSD language	24-language (English, Dutch, French, Italian, German, Spanish, Portuguese, Turkish, Polish, Russian, Swedish, Norwegian, Japanese, Simplified Chinese, Traditional Chinese, Korean, Thai, Vietnamese, Arabic, Farsi, Finnish, Indonesian, Hungarian, Greek)
--------------	---

## INPUT OUTPUT (Computer/Video/Control)

INPUT A	RGB / Y PB PR input connector: Mini D-sub 15-pin (female) Audio input connector: Stereo mini jack
---------	---

DVI input connector: DVI-D 24-pin

INPUT B	(single link), HDCP support Audio input connector: Shared with INPUT A
INPUT C	HDMI input connector: HDMI 19-pin, HDCP support Audio input connector: HDMI audio support
INPUT D	HDBaseT interface connector: RJ45, 4 play (Video, Audio, LAN, Control)
VIDEO IN	Video input connector: BNC Audio input connector: Shared with INPUT A
OUTPUT A	Monitor output for INPUT A connector: Mini D-sub 15-pin (female) Audio output connector: Stereo mini jack
OUTPUT B	Monitor output for INPUT B connector: DVD-D 24-pin (single link), HDCP not supported Audio output Monitor out connector: Stereo mini jack
REMOTE	D-sub 9-pin (male) / RS232C



---

LAN	RJ45, 10BASE-T/100BASE-TX
-----	---------------------------

---

IR (Control S)	Stereo mini jack, Plug in power DC5V
----------------	--------------------------------------

---

## Acoustic Noise

Lamp mode: Standard 28 dB

---

## Operating temperature / Operating humidity

Operating temperature / Operating humidity	0°C to 40°C (32°F to 104°F) / 20% to 80% (no condensation)
---	--

---

## Storage temperature / Storage humidity

Storage temperature / Storage humidity	-10°C to +60°C (14°F to +140°F) / 20% to 80% (no condensation)
---	--

---

## Power requirements

Power requirements	AC 100 V to 240 V, 5.0 A to 2.1 A, 50 Hz / 60 Hz
--------------------	--

---

## Power consumption

AC 100 V to 120 V	Lamp mode: High: 470 W
-------------------	------------------------

---

AC 220 V to 240 V	Lamp mode: High: 455 W
-------------------	------------------------

---

## Power Consumption (Standby Mode)

AC 100 V to 120 V	0.5 W (when "Standby mode" is set to "Low")
-------------------	---

---

AC 220 V to 240 V	0.5 W (when "Standby mode" is set to "Low")
-------------------	---

---

## Power Consumption (Networked Standby Mode)

AC 100 V to 120 V	15.0 W (All Terminals and Networks Connected) (when "Standby Mode" is set to "Standard")
-------------------	--

---

AC 220 V to 240 V	13.3 W (All Terminals and Networks Connected) (when "Standby Mode" is set to "Standard")
-------------------	--

---

## Standby Mode / Networked Standby Mode Activated

Standby Mode / Networked Standby Mode Activated	Approx. 10 Minutes
---	--------------------

---

---

## Heat dissipation

AC 100 V to 120 V	1604 BTU/h
-------------------	------------

---

AC 220 V to 240 V	1552 BTU/h
-------------------	------------

---

## Dimensions (W x H x D)

Dimensions (W x H x D)	460 x 169 x 515 mm
------------------------	--------------------

(without protrusions)	18 1/8 x 6 21/32 x 20 9/32 inches
-----------------------	-----------------------------------

---

## Mass

Mass	Approx. 13 kg (28 lb)
------	-----------------------

---

## Supplied accessories

Remote commander	RM-PJ27
------------------	---------

---

## Optional accessories

Projection Lens	VPLL-3003 / 3007 / Z3009/ Z3024 / Z3032
-----------------	---

---

## Notes

*1	With supplied standard lens.
----	------------------------------

---

\*2

This figure is expected maintenance time, not guaranteed time. The actual value depends on the environment and how the projector is used.

---

\*3

The value is average.

---

\*4

Available for VESA Reduced Blanking signal.

---

Environmental notice  
for customers in the  
USA

Lamp in this product contains mercury. Disposal of these materials may be regulated due to environmental considerations. For disposal or recycling information, please contact your local authorities or see [www.sony.com/mercury](http://www.sony.com/mercury) for additional information.

---

## Gallery

