

HXCE-FB70

Power supply extension unit for HXC-D70 and PMW-320/350/400/500 camcorders



Overview

Extends fibre connection from 250m to 10km

The HXCE-FB70 is an extension module for the fibre connection between the CA-FB70 optical fibre adaptor and HXCU-FB70 optical fibre CCU. It receives power via a fibre from the HXCU-FB70. It then connects to the CA-FB70 with a single mode fibre cable. In this case, it can extend the extension distance from 250m to 250m + 10km if the CA-FB70 is powered locally. The HXCE-FB70 is designed to work with the HXC-D70 and PMW-320/350/400/500 camcorders.

Full HD picture quality and connection for all signals

The HXCE-FB70 provides the excellent picture images as well as flexible integration and the possibility to extend the operation with all signals (Tally, Intercom, Video Return and Prompter) in full HD.

Features

Optical fibre connection

The HXCE-FB70 helps ensure the best picture quality and easy integration using optical fibre connection for distances up to 250m with power supply or up to 10km with single mode fibre and local power supply.

Connection for all signals

The HXCE-FB70 provides flexible integration and the possibility to extend the operation with all signals (Tally, Intercom, Video Return and Prompter) in full HD.

Very compact design and lightweight

The compact unit makes it easy to position in any available space in proximity of the event, while remaining inconspicuous. It is easy to carry, with a handle to help with speedy deployment and set up.

Operates with CA-FB70 and HXCU-FB70 for greater flexibility

The HXCE-FB70 can be located between the CA-FB70 optical fibre adaptor and HXCU-FB70 optical fibre CCU when power supply is required for the CA-FB70 attached to the HXC-D70 camera or PMW-320/350/400/500 camcorders, or when the long distance signal transmission is required between the CA-FB20 and HXCU-FB70.

Connector options

The HXCE-FB70 is supplied with 2x optical CON DUO connectors as standard. It is possible to adopt Lemo-type connectors as an optional alternative, using the HKC-LC02 Lemo-type fibre connector kit with the HXCU-FB70 / HXCE-FB70, or the HKC-LC01 Lemo-type fibre connector kit with the CA-FB70 / HXCE-FB70.

Related products



HXC-P70

Affordable, three 2/3-inch Exmor CMOS sensor, full HD/SD compact system camera with direct optical fibre cable connection



HXC-FB80

Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera

Gallery



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.

Export PDF : October 10 2026