

PAM-600

Projector suspension support for the
VPLFX30 and VPLFX35



Overview

Designed for the VPLFX30 and VPLFX35 Sony projectors

The PAM-600 is designed for the Sony VPLFX30 and VPLFX35 projectors, and has a load bearing capacity of 65 lb (29.48 kg). Multiple mounting options enable you to mount the projector to a 1.5-inch (3.81 cm) standard threaded pipe (NPT) or a single ceiling stud. With the help of a versatile tool, you can mount the projector on an NPT pipe by using a socket wrench and socket wrench extension. The projector can be quickly attached, and a fine tune control allows you to adjust the roll up to 5-inch to either side, pitch up to 15° down and 5° up, and yaw up to 20° left and right.

Load bearing capacity

65 lb (29.48 kg)

Features

Multiple mounting options

Enables you to mount the projector to a 1.5" (3.81 cm) standard threaded pipe (NPT) or a single ceiling stud.

Projector can be quickly attached

With the help of a versatile tool you can mount the projector on NPT pipe by using a socket wrench and socket wrench extension.

Fine tune control

Allows you to adjust the roll up to 5° to either side, pitch up to 15° down and 5° up and yaw up to 20° left and right.

Gallery



