

## AC-DN10A

AC Adapter/Charger



### Overview

- Compact and lightweight AC adaptor/charger
- Maximum 100 W DC power supply
- V-mount mechanism for direct attachment to compatible camcorders
- XLR-4-pin output to power other equipment

### Specifications

#### General

|                    |                        |
|--------------------|------------------------|
| Power requirements | 100-240 V AC, 50/60 Hz |
|--------------------|------------------------|

|                   |                 |
|-------------------|-----------------|
| Power consumption | 130 VA or lower |
|-------------------|-----------------|

|                       |                                   |
|-----------------------|-----------------------------------|
| Operating temperature | 0 °C to 35 °C<br>(32 °F to 95 °F) |
|-----------------------|-----------------------------------|

|              |                    |
|--------------|--------------------|
| Mass Approx. | 810 g (1 lb 14 oz) |
|--------------|--------------------|

|                                     |   |
|-------------------------------------|---|
| Dimensions (width / height / depth) | 101 x 177 x 48 mm<br>(4 x 7 x 1 15/16 inches) |
|-------------------------------------|---|

#### Output

|                      |  |
|----------------------|--|
| Output power (DC)    | 100 W (max.)   |
| Output voltage (DC)  | 16.7 V   |
| Output current (DC)  | 6 A (max.)<br>However, for temperatures in the range 35 °C to 45 °C (95 °F to 113 °F), the maximum output current is as follows.<br>Up to 40 °C (104 °F): 5 A (max.)<br>Up to 45 °C (113 °F): 4 A (max.) |
| Output terminal (DC) | Square 5-pin connector   |
| XLR 4-pin connector  | 16.7 V, 6 A (max.)   |
| Output terminal (DC) | Square 5-pin connector<br>16.8 V, 5 A/3 A<br>14.2 V, 5.7 A   |

## Supplied accessories

|  |   |
|--|---|
|  | Operating Instructions (1)<br>Optional accessory<br>DC power cord |
|--|---|

## Gallery

