

## SCL-PK6/F

CineAlta 4K PL mount lens pack  
x6 (feet)



### Overview

#### **Professional quality prime lenses for PMW-F55 and PMW-F5**

The SCL-PK6/F lens pack is a range of six high quality, cost effective PL mount prime lenses that work seamlessly with the PMW-F55, PMW-F5 and other CineAlta camcorders. Each lens is certified for 4K capture, while minimizing geometric distortion, vignetting, and breathing.

Pack of 20mm, 25mm, 35mm, 50mm, 85mm and 135mm lenses with calibrations in feet and inches

The set includes 6 lenses with focal lengths of 20mm, 25mm, 35mm, 50mm, 85mm and 135mm. For easy lens changes, all lenses have a consistent design, with metal casings and an aperture of T2. A 9-blade iris delivers a beautiful bokeh (the out-of-focus area of an image) and the focus ring rotates 240°.

### Features

#### **Set of 6 PL-mount prime lenses with calibrations in feet and inches (imperial)**

The SCL-PK6/F set includes 6 lenses with focal lengths of 20mm, 25mm, 35mm, 50mm, 85mm and 135mm. The SCL-PK6/M set includes the same lenses, but with metric calibrations.

#### **Delivering 4K CineAlta imaging**

---

All the PL mount prime lenses work seamlessly with the PMW-F55, PMW-F5 and other CineAlta camcorders. Each lens is certified for 4K capture, while minimizing geometric distortion, vignetting, and breathing.

## **Robust design delivers stunning performance**

The lenses have a consistent design with metal casings and an aperture of T2. A 9-blade iris delivers a beautiful bokeh (the out-of-focus area of an image) and the focus ring rotates 240°. All 3 lenses have the same compact design with the same locations of the rings, which offers a fast change of the lenses on set without moving accessories such as follow focus, etc.

## **Maximising lens flexibility of PMW-F55 and PMW-F5**

The PMW-F55 and PMW-F5 camcorders work seamlessly with the SCL-PK6/F lens pack. In addition, by removing the supplied PL mount adapter on the camcorder, a native FZ mount allows the PMW-F55 and PMW-F5 camcorders to accept FZ mount lenses directly, and SLR and DSLR lenses via third-party adapters, all without optical degradation. This provides great flexibility in lens choice.

## Gallery

