

## SNC-RS86N

Outdoor Unitized SD (NTSC)  
Rapid Dome Camera



### Overview

#### **NEW FEATURE RICH PTZ DOME FROM SONY**

Designed for outdoor use, the SNC-RS86N PTZ dome camera delivers excellent picture quality at D1 Resolution. This level of clarity combined with state-of-the-art image processing and a high speed panning capability make the RS86P one of the most effective CCTV cameras on the market. With a total tilt range of 210° and a 360° endless high-speed panning capability, it can cover a wide monitoring area quickly and in a high level of detail. This capability makes it an obvious choice for mission critical CCTV applications including airport/border and traffic surveillance.

Installation and servicing time is reduced by a newly developed base, with a Quick Release Mechanism, which means the camera can be installed or detached quickly.

SNC-RS Series Cameras also feature ONVIF (Open Network Video Interface Forum) compliance for easy interoperability with IP monitoring products from a variety of manufacturers.

#### **Capture Everything**

Sony's PTZ network dome cameras deliver clear and crisp CCTV images with a level of detail never seen before. In combination with advanced image processing technology, the SNC-RS86N provides enhanced levels of security even under the most

challenging lighting conditions. It also provides the option to cover more area with fewer cameras, depending upon your operational requirements.

### **Enhanced viewing range**

An extended tilt range provides greater viewing flexibility, especially when viewing in zoom.

### **Simple to install, easy to maintain**

The camera can be installed or detached quickly and easily thanks to its newly developed base, which greatly reduces installation and servicing time and costs.

### **High flexible network capability**

Enjoy extraordinary operational flexibility using the ideal compression format for differing image and network types (JPEG for high-quality still images; MPEG-4 and H.264 for clear, moving images over bandwidth-limited networks).

### **ONVIF compliance offers the optimum in system flexibility.**

Compliance with ONVIF (Open Network Video Interface Forum) ensures interoperability and maximum flexibility between a wide range of manufacturers' network video products.

## Features

### **Improved performance in challenging lighting conditions**

Sony's Visibility Enhancer technology improves performance in challenging lighting conditions, for example high-contrast environments, such as casinos and highways that had previously been difficult to monitor. The Visibility Enhancer's advanced system suppresses extreme whites and boosts dark areas in a scene simultaneously and dynamically, to produce clearer images on the screen.

### **Powerful optical zoom**

36 x optical zoom delivers greater flexibility in finding and tracking targets.

### **Wider vertical viewing range**

A 210° tilt angle allows a wider vertical viewing range, whilst 400°/sec pan/tilt speed and 360° continuous rotation allows users to find and track targets quickly and easily. The E-flip feature provides seamless viewing.

### **Triple Codec Network Operation**

This multi-codec camera supports three compression formats: JPEG, the best choice of high-quality still images; MPEG-4, the format that provides clear moving images efficiently over limited-bandwidth networks; and H.264, the alternative for severely limited-bandwidth networks, providing twice the efficiency of MPEG-4. The camera can generate JPEG and MPEG-4 images simultaneously

### **ONVIF Compliant**

The ONVIF (Open Network Video Interface Forum) defines a common protocol for the exchange of information between network video devices including automatic device discovery, video streaming and intelligence metadata. Allows interoperability between network video devices.

### **Tamper Alarm**

When an attempt is made to tamper with the camera, such as spray-painting the lens, the SNC-RS Series detects this and triggers an alarm. This event can also be used to activate the camera relays, or even to start the Voice Alert function.

### **Advanced Audio Detection**

Unlike conventional audio detection where an alarm is triggered based on a preset audio level, the SNC-RS Series triggers its alarms based on ambient sound conditions as the threshold. The camera stores and updates ambient audio levels and frequencies, and when the threshold level based on this data, is

surpassed, an alarm is triggered. (Available with version 1.1 or later software.)

### **Audio Message Alert**

The camera can store up to three pre-recorded audio alert messages which may be played via an active speaker upon manual or automatic initiation.

### **Audio Echo Cancellation**

This feature removes the echo frequently encountered between the operator and remote site audio systems when speakers and microphones are used.

### **IP66 Rating**

The SNC-RS86N fully complies with IP66 standard for protection against water and dust ingress, making it ideal for use in a wide range of adverse weather and environmental conditions.

### **Hard Coated Dome Cover**

Providing the optimum in protection the camera is enclosed by an impact-resistant and scratch-proof polycarbonate dome cover. Resistance to external damage ensures continued image quality and camera performance

### **Integrated Sunshade Ventilation Mechanism**

Delivering optimum performance in hot weather the conditions the camera benefits from a special ventilation mechanism

## Specifications

### Camera

Image Sensor	1/4 type CCD with Exwave HAD technology
--------------	---

Number of Effective	NTSC: Approx. 0.38 Megapixels
---------------------	-------------------------------

Pixels	PAL: Approx. 0.44 Megapixels
Signal System	NTSC
Minimum Illumination (50 IRE)	Color: 0.8 lx (XDNR ON, VE ON, Slow Shutter OFF, 50 IRE) B/W : 0.09 lx (XDNR ON, VE ON, Slow Shutter OFF, 50 IRE)
Minimum Illumination (30 IRE)	Color: 0.40 lx (F1.6, AGC ON, 1/60 s) B/W: 0.050 lx (F1.6, AGC ON, 1/60 s)
S/N Ratio (Gain 0 dB)	More than 50 dB
Gain	Auto / Manual (-3 to +28 dB)
Shutter Speed	1 s to 1/10000 s
Exposure Control	Auto, Full auto, Shutter-priority, Iris-priority, Manual, EV compensation, Backlight compensation
White Balance	Auto, Indoor, Outdoor, One-push WB, ATW, Manual
Lens	Auto-focus zoom lens
Powered Zoom	Yes
Easy Zoom	No
Zoom Ratio	Optical zoom 36x

Powered Focus	Yes
Horizontal Viewing Angle	57.8° to 1.7°
Focal Length	f = 3.4 mm to 122.4 mm
F-Number	F1.6 (wide), F4.5 (tele)
Minimum Object Distance	320 mm (wide) to 1500 mm (tele)
Pan/Tilt/Rotation Angle (manual)	360° endless rotation/ 210°
Pan Speed	400 degrees/s (max.)
Tilt Speed	400 degrees/s (max.)
Number of Preset Positions	256
Number of Tour Programs	5 preset tours, 4 shadow tours, 16 presets per one preset tour
IR Illuminator	No

## Camera Features

Day/Night	True D/N
Wide-D	DynaView
	VE (VE)

Tone Correction

---

Noise Reduction      XDNR

---

Image Stabilizer      No

---

Vandal Resistant      IK10

---

Ingress Protection      IP66

---

## Video

Resolution      720 x 480, 640 x 480, 384 x 288, 320 x 240

---

Compression Format      H.264, MPEG-4, JPEG

---

Maximum Frame Rate      H.264/MPEG-4/JPEG: 30 fps (720 x 480)

---

Multi streaming Capability      Triple streaming\*1

---

Number of Clients      10

---

## Intelligent Video/Audio Analytics

Analytics Architecture      DEPA

---

Intelligent Motion Detection      Yes

---

## Audio

Compression Format    G.711/G.726

---

## System Requirements

Operating System	Microsoft Windows XP Windows Vista (32 bit) Windows 7 (32 bit)
Processor	CPU: Pentium4 2.4 GHz, Intel Core2 Duo1.8 GHz or higher
Memory	1 GB or more
Web Browser	Microsoft Internet Explorer Ver. 6.0, Ver. 7.0, Ver. 8.0 Firefox Ver. 3.5 (plug-in free viewer only) Safari Ver. 4.0 (plug-in free viewer only) Google Chrome Ver.4.0 (plug-in free viewer only)

---

## Network

Protocols    IPv4, IPv6, TCP, UDP, ARP, ICMP,  
IGMP, HTTP, HTTPS, FTP  
(client/server), SMTP, DHCP, DNC,  
NTP, RTP/RTCP, RTSP, SNMP(MIB-

---



2)

Number of IP Address/Mac ADDRESS	1
ONVIF Conformance	Profile S
Wireless Network	Yes (with optional SNCA-CFW5)
Authentication	IEEE 802.1X

## Interface

Analog Video Output	Composite video (1.0 Vp-p) 530 TV lines
Microphone Input	Mini jack (monaural), MIC IN/LINE IN: 2.2kΩ, 2.45 V DC plug-in power
Line Input	Mini jack (monaural)
Line Output	Mini jack (monaural), Max output level : 1 Vms
Network Port	10BASE-T/ 100BASE-TX (RJ-45)
Alarm Input (Sensor Input)	x4
Alarm Output	x2
Serial Interface	RS-232C, RS-422/RS-485 (PELCO D)

	protocol)
Card Slots	CF card x 1
USB Slots	No

## General

Power Requirements	AC 24 V
Power Consumption	78 W max.
Operating Temperature	-40 to +50°C -40 to +122°F
Storage Temperature	-20°C to +60°C -4°F to +140°F
Operating Humidity	20 to 90%
Storage Humidity	20 to 95%
Dimensions (W x H x D)*2	φ238 x 344 mm φ9 3/8 x 13 5/8 inches
Mass	Approx. 4.3 kg Approx. 9 lb 8 oz
Safety Regulations	UL2044, FCC(Class A) ICES-003 Class A Digital Device IEC60950-1 EN55022(A)+EN55024+EN50130-4 JATE Technical standard (LAN),

VCCI Class A  
AN/NZS CISPR22

---

Supplied Accessories

- CD-ROM (User's Guide, SNC toolbox) (1)
- Top sunshade coupling (1)
- Belt (1)
- Bolts
- Cables
- Waterproof caps
- Warranty card (1)
- Installation Manual (1)

---

## Notes

\*1 Triple streaming (Any combination with JPEG/MPEG-4/H.264, including multiple streams of the same format)

---

\*2 The values for dimensions are approximate.

---

## Gallery

