

## MDR-M1

New reference closed monitor headphones for creators with ultra-wideband playback.



### Specifications

#### General

Type	Closed dynamic
Driver Unit	40 mm (1.58 in)
Power Handling Capacity	1,500 mW (IEC *1)
Impedance	50 $\Omega$ at 1kHz
Sensitivity	102 dB/mW
Frequency Response	5 Hz - 80,000 Hz (JEITA)
Mass	Approx. 216 g (without cable)
Included Items	Headphones cable (approx. 1.2m/2.5 m, Stereo mini plug); Plug adaptor (Stereo standard plug - Stereo mini plug); Warranty card; Reference Guide

## Notes

\*1

IEC International Electrotechnical  
Commission

---

## Related products



### **MDR-MV1**

Open back Studio  
Monitor Headphones  
for creating spatial  
and stereo sound  
with wide frequency  
range and soundstage  
feel



### **MDR-7506**

Stereo professional  
headphones

## Gallery

