

## BC-U1A

Battery charger/AC adaptor  
for BP-U90/U60/U60T/U30  
Lithium-ion battery



### Overview

#### **Charges one BP-U90/U60/U60T/U30 battery**

The BC-U1A battery charger charges one compact BP-U90, BP-U60/U60T, BP-U30 Lithium-ion battery at high speed.

#### **Built-in AC adaptor provides 12 V DC power output**

The BC-U1A also has 12 V DC power output cable to power a camcorder directly.

#### **Compact design for ease of use**

The BC-U1A has a mass of only 340 g (12 oz) and dimensions (W x H x D) of 128 x 45 x 98 mm (5 1/8 x 1 13/16 x 3 7/8 inches).

NOTE: BC-U1A is compliant with safety standard IEC62368-1.

### Specifications

#### General

Power Requirements	AC100V ~ 240V 50/60Hz
--------------------	-----------------------

Power consumption	46W
-------------------	-----

DC supply	[36W] 12V / 3.0A
-----------	------------------

Charging Voltage	16.4V
Dimensions (W x H x D)	128x45x98 (mm)
Mass	340 (g)
Operating Temperature	[DC supply]-5 °C ~ +45°C [Charge] 0°C ~ +45°C

## Approximate charge times

BP-U90	190 minutes
BP-U60	150 minutes
BP-U30	130 minutes

## Supplied Accessories

Supplied Accessories	Instruction manual Warranty Paper
----------------------	--------------------------------------

## Related products



### PXW-FS7

4K Super 35mm Exmor CMOS sensor XDCAM camera with α Mount lens system, 4K/2K RAW and XAVC recording options



### PXW-X200

Three 1/2-type Exmor™ CMOS Full HD sensor XDCAM camcorder with 17x zoom lens and XAVC recordings



### PXW-FS7M2

4K Super 35mm Exmor CMOS sensor XDCAM camera with Variable ND Filter, E-Mount (Lever Lock), 4K/2K RAW and XAVC recording



### PXW-X180

Three 1/3-inch type Exmor™ CMOS Full HD sensor XDCAM camcorder with 25x zoom lens and wireless operations, including XAVC recordings



## PXW-Z280

World's first 4K Handheld Camcorder with 1/2-type 3CMOS with 4K 50p/60p recording capability, 12G-SDI, Dual Link Cellular capability, 17x zoom lens, advanced Face Detection AF



## PXW-FS5

Grab and Shoot with handheld Super 35



## PXW-Z190

4K Handheld Camcorder with all-new 1/3-type 3CMOS with 4K 50p/60p\* recording capability, 25x zoom lens and advanced Face Detection AF



## PXW-X160

Three 1/3-inch type Exmor™ CMOS Full HD sensor XDCAM camcorder with 25x zoom lens and XAVC recordings



## PMW-300K1

Three 1/2-inch Exmor™ CMOS sensors semi-shoulder XDCAM camcorder with interchangeable 14x zoom HD lens system recording XAVC HD 100 Mbps and MPEG HD422 at 50 Mbps



## PXW-FS5M2

'Grab and shoot' Super35 handheld camcorder with stunning new creative look, 4K 120fps HFR and HDR, α Mount lens system, Variable ND Filter, 4K/2K RAW and XAVC recording



## PMW-300K2

Three 1/2-inch Exmor™ CMOS sensors semi-shoulder XDCAM camcorder with interchangeable 16x zoom HD lens system recording XAVC HD 100 Mbps and MPEG HD422 at 50 Mbps

## Gallery

