

# Betacam SX



**Strengthened base film for more robust tape.**

**Thinner tape allows increased recording time.**

**Refined high density particle packing and advanced calendaring systems optimises tape surface.**

**Ultra fine magnetic particles for high output**

**High durability and long head life, even under punishing conditions**

**Cleaning Tape: BCT-5CLN**

## General Characteristics

Master Carton Quantity (piece)	BCT-194SXLA: 10 BCT-184SXLA: 10 BCT-124SXLA: 10 BCT-94SXLA: 10 BCT-64SXLA: 10 BCT-62SXA: 50 BCT-32SXA: 50 BCT-22SXA: 50 BCT-12SXA: 50 BCT-6SXA: 50
Master Carton Weight (kg)	BCT-194SXLA: 7.7 BCT-184SXLA: 7.6 BCT-124SXLA: 7 BCT-94SXLA: 6.8 BCT-64SXLA: 6.5 BCT-62SXA: 15.2 BCT-32SXA: 13.8 BCT-22SXA: 13.3 BCT-12SXA: 12.8 BCT-6SXA: 12.6
Playing time (min)	BCT-194SXLA: 194 BCT-184SXLA: 184 BCT-124SXLA: 124 BCT-94SXLA: 94 BCT-64SXLA: 64 BCT-62SXA: 62 BCT-32SXA: 32

BCT-22SXA: 22  
 BCT-12SXA: 12  
 BCT-6SXA: 6

Tape length (m)

BCT-194SXLA: 707  
 BCT-184SXLA: 671  
 BCT-124SXLA: 456  
 BCT-94SXLA: 349  
 BCT-64SXLA: 241  
 BCT-62SXA: 231  
 BCT-32SXA: 124  
 BCT-22SXA: 88  
 BCT-12SXA: 52  
 BCT-6SXA: 31

Weight (g)

BCT-194SXLA: 720  
 BCT-184SXLA: 710  
 BCT-124SXLA: 655  
 BCT-94SXLA: 630  
 BCT-64SXLA: 600  
 BCT-62SXA: 270  
 BCT-32SXA: 240  
 BCT-22SXA: 230  
 BCT-12SXA: 220  
 BCT-6SXA: 215

### Magnetic Properties

Intrinsic coercivity (kA/m)	125.0
Retentivity (mT)	245.0
Squareness (Br/Bm)	0.85

### Physical Properties

Thickness: backcoating (μm)	1.0
Thickness: base (μm)	11.0
Thickness: magnetic layer (μm)	2.0
Thickness: total (μm)	14.0
Width (mm)	12.65

