

## ODBK-201

\*Please contact your local sales representative for details.



### Overview

**The ODBK-201 is a power supply for the ODS-L30M/L60.**

**The ODBK-20X series can drive the ODS-D280F and the ODS-D77F.**

**A world of solutions**

### Related products



#### **ODS-L30M**

\*Please contact your local sales representative for details.



#### **ODS-L60E**

\*Please contact your local sales representative for details.



#### **ODS-L100E**

\*Please contact your local sales representative for details.



#### **ODS-D280F**

Optical Disc Archive fibre channel drive unit for the ODS-L30M/L60E/L100E PetaSite scalable library with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge



#### **ODS-D77F**



#### **ODS-**

Optical Disc Archive  
fibre channel drive  
unit for ODS-L30M  
PetaSite scalable  
library with transfer  
speeds up to 1,150  
Mbps (read) and 780  
Mbps (write-once  
disc) or 310 Mbps  
(rewritable disc)

## **D380F**

\*Please contact your  
local sales  
representative for  
details.

## Gallery

