

Optical Disc Archive Cartridge Generation 2



Reliable and robust large-capacity media for Optical Disc Archive, Generation 2

Capacity 3.3TB

Double sided disc with triple layer/side achieving a large 3.3TB big capacity whilst maintaining the same size cartridge of 1st generation ODA.

Higher Transfer rate

Maximum transfer rate (1Gbps/write, 2Gbps/read) is achieved by double sided disc and a new pick up system.

Reliable archival media

Archival Disc contains a special recording layer with an excellent level of corrosion and oxidation resistance. It has a long archival life span and is highly suitable for your archival use.

Specifications

Disc	Archival Disc
Total capacity	3300 GB (3.3TB)
Recording layer	Double sided Disc with Triple layer/side
Recording method	Land & Groove recording
Recording type	Write Once
Read cycle	1,000,000 cycles
Dimension	132 mm x 130mm x 26.7mm
Operating conditions	5 ~ 55 deg.
Storage conditions	-10 ~ 55 deg. / 3 ~ 90%RH (Short term) 10 ~ 30 deg. / 30 ~ 70%RH (Long term *recommended)
Archival life	100 year(estimated)



