

UP-X898MD

A6 Analogue and Digital Black and White Thermal Printer



Overview

High speed, high quality black & white printing of medical images in a compact space-saving footprint with analogue and digital inputs

The UP-X898MD is a compact A6 medical grade black and white digital printer that can accept analogue video as well as PC-friendly digital USB signal inputs.

It's designed to be integrated into a wide range of compatible medical imaging environments such as digital ultrasound systems, mobile C-arms or cardiac catheterisation laboratory. The high quality thermal print engine can produce hard copy prints of still images captured by these systems for use in patient records and referrals. For even greater convenience, printed still images can also be stored to a connected USB flash drive.

(Please note that images printed from the UP-X898MD are not to be used for diagnosis).

The UP-X898MD is a successor to the popular Sony UP-897 series of medical printers. Redesigned and upgraded, it offers several operational and ergonomic enhancements while retaining the same space-saving footprint and easy integration into medical carts. Usability is further enhanced by an enlarged LCD display panel and joystick for intuitive menu navigation.

Capable of delivering high-quality black & white prints in under two seconds. Advanced thermal printing technology delivers near-photo quality results using widely available print media.

Unique Sony technology allows paper to be cut in two directions – both up and down – as a lower cutter is newly included, along with the conventional upper cutter. This enables flexible printer installation in almost any location as well as smooth printing operations.

Wireless Printing Capability

By using the optional UPA-WU10* Wireless Print System, you can achieve cable-free connection between the Sony digital printer with 5V USB output port**, mobile C-arm and other hospital imaging modalities.

* Product availability of the UPA-WU10 may vary according to the sales area. For more information, please contact your nearest Sony sales office or an authorized dealer.

** For more information about compatible printers, please contact your nearest Sony sales office or an authorised dealer.

Features

High print quality

Advanced thermal printing technology enables photo-quality black & white prints with a high resolution up to approximately 325 dpi and grey levels up to 256 steps.

Dual cutter configuration

In addition to the conventional upper cutter, a lower cutter has been added to the front door. This enables paper to be cut in a downward direction in addition to an upward direction. This increased flexibility in cutting direction expands location choices for printer installation. For example, even if the printer is installed immediately below the operation console of an ultrasound

system, paper can easily be cut from the front. Furthermore, a safety mechanism automatically hides the lower cutter when opening the front panel to change the printing paper.

A6 prints in less than two seconds

While operating in high speed mode, the UP-X898MD can produce A6-size prints in approximately 1.9 seconds (when used with UPP-110HG or UPP-110S print media).

Hybrid operation with analogue and digital inputs

A choice of analogue composite video and PC-friendly digital USB inputs allows flexible use with a wide range of modality devices.

Store pictures on a USB flash drive

The UP-X898MD can automatically store printed images from both USB and Video inputs onto a connected USB storage device.

Compact, space-saving design

Measuring 88mm (H) x 154 mm (W) x 240 mm (D), the UP-X898MD has the same space-saving design as the UP-897MD for easy, flexible integration into medical carts.

Enhanced operability

Building on the success of the popular UP-897MD, the UP-X898MD features an enlarged LCD panel that displays printer settings, selected paper type and advisory messages. An intuitive joystick control allows speedy menu navigation, while the new Auto Lock mode prevents unintentional changes to print settings.

Hard copy reference of print settings

For convenient reference, selected settings (Brightness, Contrast, Gamma and Sharpness) can optionally be printed in a blank space on the print paper.

Uses widely available print media

Sony offers a choice of three high quality, widely available A6 thermal print media types to meet the needs of different applications. Choose from the UPP-110HD, UPP-110S, or the UPP-110HG High Glossy Printing Paper that produces glossy, long-lasting near-photo quality prints.

Wide PC compatibility

For maximum flexibility, a wide range of PC drivers are provided for Windows XP, Vista, 7 and 8 (32/64bit).

Quick guide print

Quick instruction guides for different print operations can be selected via the front control panel. They can be printed out for easy reference without needing to refer to the user manual.*

*English only.

Wireless Printing Capability*

The optional UPA-WU10 Wireless Print System allows cable-free connection between the UP-X898MD and surgical endoscopes, ultrasound systems, and other hospital imaging modalities. This is ideal for busy clinical environments, where modalities are constantly being moved between different OR and treatment rooms. This all-in-one wireless printing solution also resolves the problem of limited space on medical carts, allowing connection between a medical imaging modality and an 'off-cart' printer without requiring a lengthy USB cable.

* This function is available to Sony digital printers with USB 5V type A Output port. For more information regarding the compatibility, please contact your nearest Sony office or an authorised dealer.

Compliance with Medical Safety Standards

This product is distributed to the US and EU as a medical device and satisfies product safety standards (e.g. IEC 60601-1).

For more details, please contact your nearest Sony sales office or an authorized dealer.

Specifications

| Specifications | |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Printing Method | Direct thermal printing |
| Resolution | 325 dp |
| Gradations | 8 bits (256 levels) processing |
| Picture Elements | Digital: 4096 x 1280 dots Video NTSC: 720 x 504 dots Video PAL: 720 x 604 dots |
| Picture Area | Digital: 320 x 100 mm/12 5/8 x 3 7/8 inch (Max) STD Video NTSC: 94 x 73 mm, Video PAL: 94 x 71 mm (WIDE1) when "SIDE:OFF" is selected SIDE Video-NTSC: 124 x 96 mm, Video-PAL: 127 x 96 mm (WIDE1) when "SIDE:ON" is selected |
| Paper Size | Paper width of 110 mm (4 3/8 inches) |
| Printing Time | High-speed mode: Approx. 1.9 seconds/image (at standard setting) Normal speed mode: |

| | |
|-------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| | Approx. 3.3 seconds/image (at standard setting) |
| Picture Memory | Digital: 4,096 x 1,280 x 8 (bit) Video: 10 frame memories (850 k x 8 bits per frame) |
| Interface | USB terminal (type A) for USB flash drive (X1) Hi-Speed USB (USB 2.0) (x1) VIDEO INPUT: BNC type (x1) NTSC or PAL composite video signals 1.0 Vp-p, 75 ohms (NTSC/PAL automatically discriminated) VIDEO OUTPUT: BNC type (x1) Loop-through REMOTE: Stereo mini jack (x1) |
| Printer Driver Software | Microsoft Windows 7 32/64 bit, 8 32/64 bit, 10 32/64 bit |
| Power Requirements | AC 100 V to 240 V, 50/60 Hz |
| Input Current | 1.3 A to 0.6 A |
| Operating Temperature | 5°C to 40°C (41°F to 104°F) |
| Operating Humidity | 20% to 80% (no condensation allowed) |

| | |
|-----------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Storage and Transport Temperature | -20°C to +60°C (-4°F to +140°F) |
| Storage and Transport Humidity | 20% to 80% (no condensation allowed) |
| Dimensions (W x H x D) | 154 x 88 x 240 mm (6 1/6 x 3 1/2 x 9 1/2 inches) |
| Mass | 2.5 kg (5 lb 8 oz) |
| Supplied Accessories | Thermal head cleaning sheet (1), CD-ROM (1), Before Using this Printer (1), Service Contact List (1), USB Flash Drive Ex. Cable, Print media (UPP-110HG) |

Gallery

