

CA-TX70

Digital triax adapter for HXC-D70



Overview

Enables connection via digital triax to HXCU-TX70 Camera Control Unit

The CA-TX70 digital triax adaptor for the HXC-D70 studio camera allows connection to the HXCU-TX70 digital triax Camera Control Unit (CCU). With the CCU, it is possible to control the HXC-D70 up to a maximum distance 1200 mt. with 14.5mm cable and 600 mt with 8.5mm cable, including the power and signals of Tally, Intercom, Video Return and also Prompter.

Operates with HXCU-TX70

The CA-TX70 works seamlessly with the HXCU-TX70 digital triax Camera Control Unit (CCU). The HKCU-FP2 optional front control panel can be attached onto the HXCU-TX70.

Features

Digital triax connection

The CA-TX70 helps ensure the best picture quality and easy integration of the HXC-D70 using conventional triax infrastructure up to a maximum distance 1200 mt. with 14.5mm cable and 600 mt with 8.5mm cable.

Connection for all signals

The CA-TX70 provides flexible integration and the possibility to extend the operation with all signals (Tally, Intercom, Video Return and Prompter) in full HD.

Related products



CBK-CE01

50-pin camera interface and digital extender for PMW-400/350/300



HKC-LC01

Optical fibre transmission connector



CCFN-25

25 metre optical fibre hybrid cable with opticalCON connector



CCFN-50

50 metre optical fibre hybrid cable with opticalCON connector



CCFN-100

100 metre optical fibre hybrid cable with opticalCON connector



HXC-FB80

Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.

Export PDF : October 9 2026