

## BC-U2

Two-channel simultaneous battery charger/AC adaptor for BP-U90/U60/U30 Lithium-ion battery



### Overview

#### **Charges two BP-U90/U60/U30 batteries**

The BC-U2 battery charger simultaneously charges two compact BP-U90/U60/U30 Lithium-ion batteries at high speed, providing power for XDCAM camcorders for up to six hours.\*

\* BC-U2 can charge two BP-U90 batteries in 190 minutes, each providing 85 Wh energy to power the PMW-200 or PMW-EX1R camcorder for up to 360 minutes. For full range of capacities and camcorder running times, see features.

Built-in AC adaptor provides 12 V DC power output while charging one battery

The BC-U2 also has 12 V DC power output cable to power a camcorder directly, while charging one battery simultaneously.

### Features

#### **Charges two BP-U90/U60/U30 batteries simultaneously**

The BC-U2 battery charger simultaneously charges two compact BP-U90/U60/U30 Lithium-ion batteries at high speed, providing power for XDCAM camcorders for up to six hours.

#### **Built-in AC adaptor provides 12 V DC power output while charging one battery**

The BC-U2 has 12 V DC power output cable to power a camcorder directly, while charging one battery simultaneously.

### Portable design for ease of use

The BC-U2 has a mass of 650 g (1 lb 7oz) and dimensions (W x H x D) of 177 x 53.2 x 137 mm (7 x 8 1/8 x 5 1/2 inches).

## Specifications

### Approximate charge times

BP-U90	220 minutes
BP-U60	170 minutes
BP-U30	130 minutes

### Approximate operating times (minutes) - BP-U90

PMW-F3L/K*	250
PMW-200**	360
PMW-150**	330
PMW-100**	360****
PMW-EX3***	310
PMW-EX1R**	360
PHU-220R	–

## Approximate operating times (minutes) - BP-U60

PMW-F3L/K*	170
------------	-----

PMW-200**	240
-----------	-----

PMW-150**	220
-----------	-----

PMW-100**	240
-----------	-----

PMW-EX3***	210
------------	-----

PMW-EX1R**	240
------------	-----

PHU-220R	240
----------	-----

## Approximate operating times (minutes) - BP-U30

PMW-F3L/K*	–
------------	---

PMW-200**	120
-----------	-----

PMW-150**	110
-----------	-----

PMW-100**	120
-----------	-----

PMW-EX3***	100
------------	-----

PMW-EX1R**	120
------------	-----

PHU-220R	120
----------	-----

## Notes:

The above operating times may change according to operating conditions.

---

\* Dual-Link OFF, REC mode with viewfinder.

---

\*\* REC mode with viewfinder.

---

\*\*\* REC mode with colour LCD ON.

---

\*\*\*\* When using the PMW-100 with the BP-U90 attached for extended recording periods, Sony recommends attaching the camcorder to a tripod.

---

## Gallery

