

## HZC-HFR50 / HZC-HFR50M / HZC-HFR50W

Software licenses for shooting Max. HD 8x slow motion with HDC-5500 system camera



### Overview

#### **Software licenses for shooting Max. HD 8x slow motion with HDC-5500 system camera**

HZC-HFR50, HZC-HFR50M and HZC-HFR50W are the software licenses for shooting Max. HD 8x slow motion with HDC-5500, HDC-5500V, HDC-P50A, and HDC-P50 system cameras.

HDC5500V/ HDC3500V/ HDC5500<sup>3)</sup>/ HDC3500<sup>2)</sup> 3):  
 1080/59.94P(2x), 1080/50P(2x)  
 1080/59.94P(3x), 1080/50P(3x)  
 1080/59.94P(4x), 1080/50P(4x)

HDC-P50 only:  
 1080/59.94P(6x), 1080/50P(6x)

HDC5500V/ HDC 3500V/ HDC5500/HDC3500<sup>1)</sup> / HDC5000/only:  
 1080/59.94P(6x), 1080/50P(6x)  
 1080/59.94P(8x), 1080/50P(8x)

1. To install a new format, ensure that the HKC-FB50 is integrated into a camera system that is operating on software version 2.00 or higher.
2. To install a new format, ensure that the HKC-FB30 is integrated into a camera system that is operating on software version 2.00

or higher.

3. To install a new format, ensure that the HKC-WL50 is integrated into a camera system that is operating on software version 2.00 or higher.

The HZC-HFR50 can be permanently used.

The HZC-HFR50M can be used for 30 days.

The HZC-HFR50W can be used for 7 days.

Activation key for pre-installed software.

## Gallery

