

Optical Disc Archive Cartridge Generation 2



ODC-3300R 3.3TB write-once cartridge

Overview

Reliable and robust large-capacity media for Optical Disc Archive, Generation 2

Capacity 3.3TB

Double sided disc with triple layer/side achieving a large 3.3TB big capacity whilst maintaining the same size cartridge of 1st generation ODA.

Higher Transfer rate

Maximum transfer rate (1Gbps/write, 2Gbps/read) is achieved by double sided disc and a new pick up system.

Reliable archival media

Archival Disc contains a special recording layer with an excellent level of corrosion and oxidation resistance. It has a long archival life span and is highly suitable for your archival use.

Specifications

Specifications	
Disc	Archival Disc
Total capacity	3300 GB (3.3TB)
	Double sided Disc with Triple

Recording layer	layer/side
Recording method	Land & Groove recording
Recording type	Write Once
Read cycle	1,000,000 cycles
Dimension	132 mm x 130mm x 26.7mm
Operating conditions	5 ~ 55 deg.
Storage conditions	-10 ~ 55 deg. / 3 ~ 90%RH (Short term) 10 ~ 30 deg. / 30 ~ 70%RH (Long term *recommended)
Archival life	100 year(estimated)

Related products



ODS-L30M

*Please contact your local sales representative for details.



ODS-D280U

Optical Disc Archive stand-alone drive with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge



ODS-L100E

*Please contact your local sales representative for details.



ODS-L60E

*Please contact your local sales representative for details.



ODS- D280F

Optical Disc Archive
fibre channel drive
unit for the ODS-
L30M/L60E/L100E
PetaSite scalable
library with very high
transfer speeds of
1Gbps write (verify
on) and 2Gbps read
using ODC-3300R
Generation 2 cartridge



ODS- D380F

*Please contact your
local sales
representative for
details.



ODS- D380U

*Please contact your
local sales
representative for
details.

Gallery

