

## VCL-EX0877

Wide conversion lens for PMW-EX1/1R and PMW-200



### Overview

#### **Widens the field of view for small spaces and moving camera applications**

The VCL-EX0877 is a 0.8 x wide conversion lens for the PMW-EX1/1R and PMW-200 camcorders. The lens is quickly and easily attached to the camcorder using a standard bayonet mount, giving you extra flexibility to change your shooting style. The lens provides effective protection against halation, whilst also enhancing the professional look of the image.

#### **0.8 x wide conversion lens**

For the PMW-EX1/1R and PMW-200 camcorders.

#### **Focal length 25.1mm to 351mm**

When mounted to camcorder, the focal length becomes (25.1mm to 351mm) from (31.4mm to 439mm) in 35mm equivalent.

### Features

#### **Changes focal length of camcorder**

Attaching the VCL-EX0877 to the PMW-EX1/1R and PMW-200, the focal length becomes (25.1mm to 351mm) from (31.4mm to 439mm) in 35mm equivalent.

#### **Optimise image with VCL-EX0877 with optical specification compensator function in camcorder**

By changing "Wide Conversion" in Camera Set menu "On" manually, the chromatic aberration compensation and the image stabiliser mode is optimised for the VCL-EX0877.

## Gallery

