

## SNC-UNIHB

Outdoor fixed camera housing



### Overview

#### **13- inch outdoor aluminium housing with clear window and hinged opening**

Tamper resistant camera housing with lock down screws provided. High strength steel wall mount bracket included.

#### **Flexible positioning**

Designed for mounting to a flat wall or round pole, larger than 3.5- inches in diameter.

### Features

#### **Flexible positioning**

Designed for mounting to a flat wall or round pole, larger than 3.5- inches in diameter.

#### **All-weather operation**

The unit includes a AC 24V heater and blower.

#### **Supports a variety of cameras**

Network cameras accepted: Sony's SNC-CH120/CH140/CH220/CH240 cameras. Maximum camera/lens length should not exceed 9.5 inches.

## Related products



### **SNC- VB635**

Cámara tipo caja de 1080p/60 fps con sensor CMOS Exmor™ de 1/2" con tecnología IPELA ENGINE EX™, serie V



### **SNC- VB630**

Cámara tipo caja de 1080p/60 fps con tecnología IPELA ENGINE EX™, serie V



### **SNC- VB600**

Cámara tipo caja de 720p/60 fps con tecnología IPELA ENGINE EX™, serie V



### **SNC- EB600**

Cámara tipo caja de 720p/30 fps con tecnología IPELA ENGINE EX™, serie E



### **SNC- EB630**

Cámara tipo caja de 1080p/30 fps con tecnología IPELA ENGINE EX™, serie E



### **SNC- EB520**

Cámara en red fija para interiores SD (SVGA)

## Gallery

