

SNC-UNI

Indoor fixed camera housing



Overview

13-inch indoor aluminium housing with clear window and hinged opening

Tamper resistant camera housing with lock down screws provided. High strength steel wall mount bracket included.

Flexible positioning

Designed for mounting to a flat wall or round pole, larger than 3.5 inches in diameter.

Features

Flexible positioning

Designed for mounting to a flat wall or round pole, larger than 3.5 inches in diameter.

Supports a variety of cameras

Network cameras accepted: SNC-CH120/140/220/240, SNC-ZB550, and SNC-EB520. analogue cameras accepted: SSC-FB530/560, SSC-G113A/213A and SSG-G103A/203A. Maximum camera/lens length should not exceed 9.5 inches.

Related products



SNC- VB635

Caméra fixe
1080p/60 ips avec le
capteur CMOS
Exmor™ 1/2 pouce
intégrant la
technologie IPELA
ENGINE EX - série V



SNC- VB630

Caméra fixe
1080p/60 ips avec
technologie IPELA
ENGINE EX™ - série V



SNC- VB600

Caméra fixe
720p/60 ips avec
technologie IPELA
ENGINE EX™ - série V

SNC- EB600

Caméra fixe
720p/30 ips avec
technologie IPELA
ENGINE EX™ - série E

SNC- EB630

Caméra fixe
1080p/30 ips avec
technologie IPELA
ENGINE EX™ - série E

SNC- EB520

Caméra réseau fixe
d'intérieur SD (SVGA)

Gallery

