

## SNC-UNI

Indoor fixed camera housing



### Overview

#### **13-inch indoor aluminium housing with clear window and hinged opening**

Tamper resistant camera housing with lock down screws provided. High strength steel wall mount bracket included.

#### **Flexible positioning**

Designed for mounting to a flat wall or round pole, larger than 3.5 inches in diameter.

### Features

#### **Flexible positioning**

Designed for mounting to a flat wall or round pole, larger than 3.5 inches in diameter.

#### **Supports a variety of cameras**

Network cameras accepted: SNC-CH120/140/220/240, SNC-ZB550, and SNC-EB520. analogue cameras accepted: SSC-FB530/560, SSC-G113A/213A and SSG-G103A/203A. Maximum camera/lens length should not exceed 9.5 inches.

### Related products



## **SNC- VB635**

Caméra fixe  
1080p/60 ips avec le  
capteur CMOS  
Exmor™ 1/2 pouce  
intégrant la  
technologie IPELA  
ENGINE EX - série V



## **SNC- VB630**

Caméra fixe  
1080p/60 ips avec  
technologie IPELA  
ENGINE EX™ - série V



## **SNC- VB600**

Caméra fixe  
720p/60 ips avec  
technologie IPELA  
ENGINE EX™ - série V

## **SNC- EB600**

Caméra fixe  
720p/30 ips avec  
technologie IPELA  
ENGINE EX™ - série E

## **SNC- EB630**

Caméra fixe  
1080p/30 ips avec  
technologie IPELA  
ENGINE EX™ - série E

## **SNC- EB520**

Caméra réseau fixe  
d'intérieur SD (SVGA)

## Gallery

