

SNC-UNI

Indoor fixed camera housing



Overview

13-inch indoor aluminium housing with clear window and hinged opening

Tamper resistant camera housing with lock down screws provided. High strength steel wall mount bracket included.

Flexible positioning

Designed for mounting to a flat wall or round pole, larger than 3.5 inches in diameter.

Features

Flexible positioning

Designed for mounting to a flat wall or round pole, larger than 3.5 inches in diameter.

Supports a variety of cameras

Network cameras accepted: SNC-CH120/140/220/240, SNC-ZB550, and SNC-EB520. analogue cameras accepted: SSC-FB530/560, SSC-G113A/213A and SSG-G103A/203A. Maximum camera/lens length should not exceed 9.5 inches.

Related products



SNC- VB635

Telecamera fissa da 1080p/60 fps dotata di sensore CMOS Exmor™ da 1/2" con tecnologia IPELA ENGINE EX™ - Serie V



SNC- VB630

Telecamera tipo box da 1080p/60 fps con tecnologia IPELA ENGINE EX™ - Serie V



SNC- VB600

Telecamera tipo box da 720p/60 fps con tecnologia IPELA ENGINE EX™ - Serie V

SNC- EB600

Telecamera tipo box da 720p/30 fps con tecnologia IPELA ENGINE EX™ - Serie E

SNC- EB630

Telecamera tipo box da 1080p/30 fps con tecnologia IPELA ENGINE EX™ - Serie E

SNC- EB520

Telecamera fissa SVGA - Serie E

Gallery

