

VCL-EX0877

Wide conversion lens for PMW-EX1/1R and PMW-200



Panoramica

Widens the field of view for small spaces and moving camera applications

The VCL-EX0877 is a 0.8 x wide conversion lens for the PMW-EX1/1R and PMW-200 camcorders. The lens is quickly and easily attached to the camcorder using a standard bayonet mount, giving you extra flexibility to change your shooting style. The lens provides effective protection against halation, whilst also enhancing the professional look of the image.

0.8 x wide conversion lens

For the PMW-EX1/1R and PMW-200 camcorders.

Focal length 25.1mm to 351mm

When mounted to camcorder, the focal length becomes (25.1mm to 351mm) from (31.4mm to 439mm) in 35mm equivalent.

Attributi

Changes focal length of camcorder

Attaching the VCL-EX0877 to the PMW-EX1/1R and PMW-200, the focal length becomes (25.1mm to 351mm) from (31.4mm to 439mm) in 35mm equivalent.

Optimise image with VCL-EX0877 with optical specification compensator function in camcorder

By changing "Wide Conversion" in Camera Set menu "On" manually, the chromatic aberration compensation and the image stabiliser mode is optimised for the VCL-EX0877.

Galleria

