

UNI-OPL7C3

Outdoor Pressurized dome camera housing



Overview

Applicable Camera Models;
- SNC-RX550P - SNC-RX530P - SNC-RX570P Fixing Method;
- SNCA-WM20G (wall) -SNCA-CEILING (ceiling) -SNCA-WM20FC (see note) Rating;
-IP67 Operating Temperature;
--29°C to +50°C (SNCA-HEATER) Voltage;
-24 volts AC Optional accessories;
-SNCA-CLEAR/2 (included)
-SNCA-TINTED/2

Related products



SNC-EB600

Telecamera tipo box da 720p/30 fps con tecnologia IPELA ENGINE EX™ - Serie E



SNC-EB600B

Telecamera tipo box entry-level da 720p/30 fps con tecnologia IPELA ENGINE EX™ - Serie E



SNC-EB630

Telecamera tipo box da 1080p/30 fps con tecnologia IPELA ENGINE EX™ - Serie E



SNC-EB630B

Telecamera tipo box entry-level da 1080p/30 fps con tecnologia IPELA ENGINE EX™ - Serie E



SNC-



SNC-



SNC-



SNC-

VB600

Telecamera tipo box da 720p/60 fps con tecnologia IPELA ENGINE EX™ - Serie V



EP521

Telecamera di rete PTZ a Definizione Standard (PAL)



EP580

Telecamera PTZ da 1080p/30 fps serie E

ER521

Telecamera di rete rapid dome a Definizione Standard (PAL)

SNC-ER550

Telecamera rapid dome da 720p/30 fps serie E

SNC-ER580

Telecamera rapid dome da 1080p/30 fps serie E

Gallery

