

LMD-XH550MD

55 4K 2D



Specifications

	TFT LCD
()	1387.8mm(54 3/4)
(H x V)	1209.6 x 680.4mm(47 5/8 x 26 7/8)
	0.315 x 0.315mm(0.0124 x 0.0124)
(H x V)	3,840 x 2,160
	16:9
	99.99%
	LED
	LCD(IPS)
()	1500cd/m ² (,)
	1,000,000:1()
	10 (1,073,741,824)

	50/60Hz
()	89°/89°/89°/89°()(/ / / > 10:1)
	1.8, 2.0, 2.2, 2.4, 2.6, DICOM, , HLG
HDMI	HDMI(x1)(HDCP 2.3)
DVI-D	DVI-D(x1)(TMDS , HDCP 1.4)
SDI	BNC(x2) 12G/3G/HD-SDI, BNC(x1) 3G/HD/SD-SDI
	(x1)(SST HDCP 1.3)
(LAN)	D-sub 9(RS-232C)(x1), RJ-45(x1)(, 10BASE- T/100BASE-TX)
	(x1)
AC	AC (x1) AC 100~240V, 50/60Hz
DC	-
SDI	BNC(x2) 12G/3G/HD-SDI, BNC(x1) 3G/HD/SD-SDI
	BNC(x1) 12G/3G-SDI

DC 5V/12V	5V (x1) 2.0A , 12V (x1) 2.5A
	AC IN: 100V~240V, 50/60Hz, 3.1A~1.1A
	290W()
	0°C ~ 40°C(32°F ~ 104°F)
	30% ~ 85%()
/	-20°C ~ +60°C(-4°F ~ +140°F)
/	20% ~ 90%
//	700hPa ~ 1060hPa
(W x H x D)	1249.6 x 763.3 x 92.8mm 49 1/4 x 30 1/8 x 3 3/4
	25kg(55lb 1.8oz)
(W x H)	200 x 200mm, 400 x 200mm
IP	IP45()/IP32()



AC (1),
AC plug holder(2),
(1)
CD-ROM()(1),
(1),

M6 x 12mm (4)

Related
products



**LMD-
XH550MT**

55 4K 3D/2D LCD



**LMD-
XH320MT**

32 4K 3D/2D LCD



**HVO-
4000MT**

4K 2D/3D



**MCC-
1000MD**

2 Full HD

Gallery

