

## UNI-OTBC2

Temperature-controlled vandal resistant outdoor security camera housing



### Overview

This vandal-resistant housing is compatible with Sony SNC-EB6xx and SNC-VB6xx series box-type security cameras.

Suitable for wall or pole mounting outdoors, the UNI-OTBC2 meets NEMA Type 4 and IP66 standards for resistance to dust/moisture penetration. It's also IK10 impact rated.

Ideal for use in a wide range of climatic environments, the camera housing features an adjustable sunshield plus a thermostatically controlled heater and fan cooling system.

Operating voltage 24V AC or 12V DC.

### Related products



#### **SNC-EB600**

Cámara minidomo de 720p/30 fps alimentada por IPELA ENGINE EX™ - Serie E



#### **SNC-EB600B**

Cámara tipo caja básica de 720p/30 fps alimentada por IPELA ENGINE EX™ - Serie E



#### **SNC-EB630**

Cámara minidomo de 1080p/30 fps alimentada por IPELA ENGINE EX™ - Serie E



#### **SNC-EB630B**

Cámara tipo caja básica de 1080p/30 fps alimentada por IPELA ENGINE EX™ - Serie E



## **SNC- EB640**

Cámara IP Full HD en red tipo caja (Serie E)



## **SNC- VB600**

Cámara minidomo de 720p/60 fps alimentada por IPELA ENGINE EX™ - Serie V



## **SNC- VB600L**

Cámara minidomo de 720p/60 fps alimentada por IPELA ENGINE EX™ - Serie V



## **SNC- VB630**

Cámara minidomo de 1080p/60 fps alimentada por IPELA ENGINE EX™ - Serie V



## **SNC- VB635**

Cámara tipo caja de 1080p/60 fps con sensor CMOS Exmor™ de 1/2" y tecnología IPELA ENGINE EX™ Serie V



## **SNC- VB640**

Cámara IP Full HD en red tipo caja 1080p/60fps (Serie V)

## Gallery

