

SRPC-5

SRMASTER Data Transfer Unit



Краткое
содержание

The SRPC-5 is a cost-effective solution for SRMemory data viewing, logging, and ingesting to off-line editing applications.

The unit offers a web-based GUI, which is used for viewing and ingesting SRMemory content for review on-set and at post-production facilities. It can ingest recorded data to servers and to non-linear editors (NLEs).

In addition, it can duplicate valuable materials from SRMemory to HDCAM SR tape.

Характеристики

Fast ingest

The SRPC-5 allows fast data transfer from SRMemory cards to servers and/or NLEs via an optional 10 GbE network interface. Files and clips can be easily browsed by the SRPC-5 GUI.

It also enables fast ingest from HDCAM SR tapes, at up to twice* the normal playback speed.

*Refers to MXF Files.

Simple Viewing

When material is recorded in SR Video mode, you can browse and view the contents on a broadcast monitor.

Flawless Tape backup

Content on SRMemory can be duplicated to HDCAM SR tape without any decode/re-encode processes. You can simply duplicate a whole SRMemory card or select individual clips to be perfectly cloned.

Характеристики

General	
Power Requirements	100 to 240 V AC (50/60 Hz)
Power Consumption	Approx. 110 W (with all options)
Operating Temperature	5°C to 40°C
Operating Temperature	41°F to 104°F
Storage Temperature	-4°F to +140°F
Storage Temperature	-20°C to +60°C

General

Mass	22 lb
Mass	10 kg
Dimensions (W x H x D) *[1]	427 x 43.6 x 546 mm (excluding protrusion)
Dimensions (W x H x D) *[1]	16 7/8 x 1 3/4 x 21 1/2 inches (excluding protrusion)

Input/Output

AUX Input	Input for uncompressed video data dubbing between SRW-5800
AUX Input	BNC (x2)
AUX Output	HD-SDI (1.485 Gbps) (SMPTE 292M/372M, BTA-S004B standard)
AUX Output	B: BNC (x1)
AUX Output	A: BNC (x1)
AUX Output	3G-SDI (2.97 Gbps) (SMPTE 424M)
VTR Interface	Local Interface Output A/B: BNC (x2)
VTR Interface	Local Interface Input A/B: BNC (x2)
Network	RJ-45 jack (x1) 1000BASE-T
Option	PCI Express Slot (x1) (PCI Express x4 Gen1)

On-board Function

On-board Function	1D LUT, Down converter, Color space converter
-------------------	---

Supplied Accessories

Supplied Accessories	Rack mount angle (1) (An optional RMM-10 Rack Mount Kit is necessary to mount the unit on a rack.)
Supplied Accessories	Washers (4)
Supplied Accessories	SR Viewer (CD-ROM) (1)
Supplied Accessories	Screws (4)
Supplied Accessories	Operation manual (1)
Supplied Accessories	Operation guide (1)
Supplied Accessories	Installation manual (1)
Supplied Accessories	AC power cord (1)

Confirmed Operational Environment

Browser	Firefox, Internet Explorer, Safari, Google Chrome
NFS Server	Redhat Linux E5, Mac OS v10.6
CIFS Server	Windows XP, Windows 7

Notes

Note	*[1] The values for dimensions are approximate.
------	---

Галерея

