

## UNI-OFS7T1

7-inch outdoor vandal-resistant tinted flush-mount housing with heater/blower for SNC-RH124, SNC-RS44N, SNC-RS46N, SNC-RX series and SNC-RZ25N PTZ cameras, DC 12V power



### Overview

#### **Outdoor vandal resistant flush mount enclosure with thermostatically controlled heater/ blower**

The flush-mount 7-inch vandal resistant rugged housing offers versatility and camera protection in a compact size. These outdoor surface mount enclosures can be mounted facing down or facing up toward the sky. The housing is available with a tinted dome. DC 12V input is required for the heater.

#### **Tinted dome**

7-inch polycarbonate.

### Features

#### **Outdoor vandal resistant flush mount housing**

7-inch tinted polycarbonate lower dome.

#### **Thermostatically controlled heater and blower**

DC 12V input.

## Gallery

