

BVM-L231

23-inch Reference LCD monitor



Краткое содержание

The BVM-L231 reference LCD monitor supersedes the market leading BVM-A series CRT models, heralding in a new era in broadcast post-production, D-Cinema production, evaluation and mastering. A premium Sony technology - TRIMASTER - is used in the BVM-L231 to produce an LCD monitor fully justifying the Reference designation. In developing TRIMASTER, the technology had to deliver accurate colour reproduction, precision imaging and absolute picture consistency. Sony has achieved this through 3 key devices: a high-grade customised LCD Panel, a precision High-Purity LED Backlight system and a sophisticated Display Engine.

The high-grade customised LCD panel incorporates a 10-bit driver for smooth greyscale and colour transitions, and possesses a high frame rate allowing black-frame insertion for reduced motion blur.

The Precision Backlight system uses High Purity LEDs - delivering wide reference-standard colour space, uniformity control and colour stability through the auto white-balance circuitry.

The display engine uses 2 state-of-the-art ICs employing accurate 12-bit output processing - one dedicated to I/P conversion, producing the lowest possible artefact count, and one focussed on the highly accurate colour management system, delivering stability, consistency and precise standards emulation. The BVM-L231 also benefits from picture and picture and blend modes plus a pixel zoom function for greater user flexibility. The BVM-L231 accepts all video formats up to 3G SDI with the optional BKM-250TG input board. It is also equipped with HDMI interface as standard.

Finally, a new backlight scanning system is integrated to improve the black level reproduction when Black Frame insertion mode is selected. With its exceptional performance and the advantages of LCD, the BVM-L231 is a deserving successor to CRT broadcast reference monitors.

Suitable for a Wide Range of Reference and Mastering Applications

Ideal for BROADCAST (studio and engineering etc.), PRODUCTION (OB, monitor wall, camera and VTR control etc.), and POST-PRODUCTION (top-end multi-format editing consoles, telecinema and digital cinema).

Ultimate Picture Quality Rivalling Top-Flight CRT Monitors

The BVM-L231 is capable of displaying High Definition native 1920x1080 picture resolution on its LCD display. Taken together with its customised LCD panel and 10-bit drivers for smooth colour gradation, its precision LED backlight for wide colour gamut and picture consistency, and its new 12-bit output display engine processor for accurate colour reproduction and sophisticated I/P conversion, the BVM-L231 is truly the standard-bearer amongst reference LCD monitors.

Superb Colour Accuracy

The innovative Colour Management System ensures consistent and repeatable colour to ITU-709, SMPTE-C and EBU standards and from monitor to monitor. The level of accuracy is the same as displayed by the BVM-A series of CRT monitors.

Outstanding Greyscale and Colour Depth Provide Lifelike Picture Quality

Achieved through 10-bit LCD panel drivers and 12-bit output signal processing.

Picture Quality Decisions can be made with Confidence

The BVM-L231 Monitor's exceptional performance in the key areas of picture quality, accuracy, consistency and stability make this product a natural choice as a measurement and reference tool.

Consistently Optimal Picture Performance

Less 'drift' than CRT displays, with an absence of picture distortions such as convergence, geometry, linearity and focus variation. The BVM-L231 is also immune to magnetic field interference.

Faithful Reproduction of Interlaced Pictures

Capable of reproducing interlaced video images to the same standard as CRT monitors.

High Quality Motion Display

Black Frame Insertion Mode dramatically reduces motion blur.

Exemplary Picture Consistency

Consistent and repeatable chroma and greyscale performance ensures efficient matching between monitors.

Productivity Boost

New dual image processing including Picture Side by Side, Wipe, Butterfly, Blending modes and a new Pixel Zoom mode allow quick evaluation and comparison of two input sources.

Exceptionally Versatile

Due to its broad range of inputs and multi-format signal capabilities, the BVM-L231 is equally suited to AV or IT-based applications, allowing you the freedom to operate in whichever format you choose, even D-Cinema.

Future Proof

Multi-format and HD capability plus optional decoder boards will ensure that the BVM-L231 remains current.

Easier to Install and Accommodate than CRT

Space saving / lightweight / low heat output

Air Conditioning Requirements lower than with CRT

LCD monitors generate less heat.

Easy Maintenance

No routine convergence, focus, geometry or linearity adjustments necessary. No susceptibility to magnetic fields.

Lower Total Cost of Ownership than CRT

Long operational life / high reliability.
Low energy bills.
Low routine maintenance cost
Reduced environmental disposal costs.

Характеристики

Full HD Panel with 10-bit Driver

The BVM-L231 achieves both high resolution and stunning colour depth using a full 1920 x 1200 HD LCD panel and precise 10-bit drivers. It delivers outstandingly crisp, high brightness and high contrast HD images in Native mode.

LCD Panel Calibration

Each and every BVM-L231 monitor is carefully calibrated at the factory on an individual basis, providing a high level of accuracy and stability for characteristics such as gamma and uniformity.

Ultra-high Precision Uniformity Correction

White can be reproduced uniformly at every point of the screen on the BVM-L231. This is due to the use of two advanced technologies: precise adjustment of the LCD panel characteristics and sophisticated LED backlight control.

High-Purity Precision LED Backlight

Provides an exceptionally broad colour gamut for faithful colour display, as well as delivering precise picture uniformity and stability.

Nonlinear Cubic Conversion Colour Management System

The nonlinear cubic conversion colour management system uses a unique 3D LUT to reproduce an extremely wide colour gamut, thus offering more accurate colour reproduction.

Accurate, Repeatable and Stable Colour Reproduction

The innovative precision LED backlight and Colour Management System deliver accurate and consistent colour temperature right across the greyscale range. Consequently, the monitor can emulate ITU-709, SMPTE-C, and EBU colour spaces with ease. It can also emulate D-Cinema colour gamut

Auto White-Balance Function

The BVM-L231 can perform automatic colour temperature adjustments when connected to an external colour analyzer (such as those from Minolta, DK and X-Rite).

High Accuracy Display Engine

The BVM-L231 uses a 12-bit output display engine, which allows images to be reproduced with high precision for accurate evaluation and manipulation.

Sophisticated Interlace to Progressive Algorithm

The BVM-L231 uses a sophisticated I/P conversion technique that keeps artefacts that are often seen in typical LCD monitors to a minimum, such as edge jaggedness, conversion errors, and ensure a picture delay that is less than one field.

Interlace Display Mode

Faithfully reproduces interlaced signals, emulating CRT monitors.

Input Versatility

The BVM-L231 can accept almost any SD or HD video format, both analogue and digital, plus PC signals from VGA to WUXGA (1920 x 1200). In addition to a HDMI and DVI-D interface equipped as standard, four option board slots are offered to configure the BVM-L230 monitor according to different user needs.

Multi-Format Signal Support - Up to 3G SDI

The BVM-L231 is capable of displaying an exceptionally broad range of signal formats with an extremely high degree of colour accuracy. These include: composite video formats NTSC, PAL &

3G SDI Input

The BVM-L231 has a 3G SDI input capability. On Sony's monitors, the 3G SDI interface is compliant with the SMPTE 425 standard, transmitting up to 4:2:2/10-bit 1080/60P video data using one SDI cable. This single-link system is known as a SD-SDI or HD-SDI system, but it can also handle both Dual-Link HD-SDI and 3G SDI video data with the use of Sony's 3G SDI interface. This 3G SDI interface enables the BVM-L231 monitor to accept 50P and 60P video data. Where an upgrade to a Dual-Link HD-SDI system is necessary, this single-link 3G SDI system is the ideal alternative.

Dual Image Processing

Image Side by Side, Wipe, Butterfly and Blend modes provide users with enhanced operational flexibility.

New Pixel Zoom Mode

Allows picture magnification up to 800% without scaling.

Black Frame Insertion Mode

Dramatically reduces motion blur - a problem common to many LCD monitors.

S-Log Gamma

S-Log is the original logarithmic gamma developed for the F35 series CineAlta camera. It enables to transmit the full Dynamic of the camera over 700%. The monitor S-Log anti Gamma function allows displaying the full dynamic range on the screen.

Separate Control unit with memory stick slot

The Memory Stick socket located in the BKM-16R control unit enables users to download and save all monitor set-ups such as input channel configuration, control preset adjustments, white balance settings and maintenance parameters.

Centralised Monitor-Wall Control

Multiple monitors can be easily managed by a single control unit via a serial RJ45 Ethernet connector.

Характеристики

Picture Performance	
Panel	a-Si TFT Active Matrix LCD
Picture Size (Diagonal)	570.6 mm
Picture Size (Diagonal)	22 1/2 inches
Effective Picture Size (H x V)	483.8 x 302.4 mm
Effective Picture Size (H x V)	21 1/2 x 12 1/8 inches
Resolution (H x V)	1920 x 1200 pixels (WUXGA)
Aspect	16:10
Pixel Efficiency	0.9999
Backlight	High-purity LEDs
Panel Drive	RGB 10-bit
Panel Frame Rate	96 Hz, 100 Hz, 120 Hz
Viewing Angle (Panel Specification)	89°/89°/89°/89° (typical) (up/down/left/right contrast > 10:1)
Normal Scan	0% scan
Native Scan	Mapping the pixels of the signal to the panel to one-to-one mode, or displaying an SD signal of nonsquare pixels (the number of H pixels of the signal system is 720 or 1440) or a 640 × 480 SD signal of HDMI video by scaling processing of doubling for the V direction and correct aspect ratio for the H direction and also optimizing and sidplaying a picture by modifying the aperture coefficient value, filter coefficient value, etc.
Under Scan	3% under scan

Picture Performance

Over Scan	Mask of 5% over scan portion in the normal scan
Color Temperature	D55, D61, D65, D93, D-Cine (48 Hz, 60 Hz and 72 Hz are also compatible with a frame rate of 1/1.001.), User
Standard Luminance	100 cd/m ² (Preset1 to Preset5)
Standard Luminance	48 cd/m ² (Preset (D-Cine))
Standard Luminance	(100% white signal input)
Color Space (Color Gamut)	ITU-R BT.709, EBU, SMPTE-C,
Color Space (Color Gamut)	D-Cine (D-Cine: $x = 0.314$, $y = 0.351$), L23 Nativ (The SRM-L560 individual chromaticity points. The widest color space setting of the signal is reproduced by the SRM-560. R ($x = 0.663$, $y = 0.313$)/G ($x = 0.233$, $y = 0.654$)/B ($x = 0.150$, $y = 0.060$) (typical))
Color Space (Color Gamut)	S-GAMUT (The BVM-E250 individual chromaticity points. The widest color space setting of the signal is reproduced by the BVM-E250. R ($x = 0.681$, $y = 0.319$)/G ($x = 0.189$, $y = 0.724$)/B ($x = 0.141$, $y = 0.051$) (typical))
Warm-up Time	Approx. 30 minutes

Input

HDMI Input	HDMI (x1) (HDCP correspondence, Deep Color correspondence)
DVI-D Input	DVI-D (x1) (HDCP correspondence)
Option Port	Four (4) ports
Parallel Remote	D-sub 9-pin (female) (x1)
Serial Remote (LAN)	RJ-45 (x1) (Ethernet, 10BASE-T/100BASE-TX)
Option A Input	Mini-DIN 8-pin (female) (x1)
Option B Input	USB (Type A) (x1) (used for future expansion)

Output

DC 5 V Output	Circle 4-pin (female) (x1)
---------------	----------------------------

General

Power Requirements	100 V to 240 V AC, 2.0 A to 0.9 A, 50/60 Hz
Power Consumption	Approx. 180 W (max.)

General

Power Consumption	Approx. 130 W (with BKM-243HS, average power consumption in the default status)
Inrush Current	(1) Power ON, current probe method:
Inrush Current	20 A (100 V), 52 A (240V)
Inrush Current	(2) Hot switching inrush current, measured in accordance with European standard EN55103-1:
Inrush Current	25 A (230 V)
Operating Temperature	0°C to 35°C (Recommended: 20°C to 30°C)
Operating Temperature	32°F to 95°F (Recommended: 68°F to 86°F)
Operating Humidity	0% to 90% (no condensation)
Storage/Transport Temperature	-20°C to +60°C
Storage/Transport Temperature	-4°F to +140°F
Storage/Transport Humidity	0% to 90%
Operating/Storage/Transport Pressure	700 hPa to 1060 hPa
Dimensions (W x H x D) [*1]	565.5 x 436.4 x 243.1 mm
Dimensions (W x H x D) [*1]	22 3/8 x 17 1/4 x 9 5/8 inches
Mass	Approx. 21.0 kg
Mass	Approx. 46 lb 5 oz
Supplied Accessories	AC power cord (1)
Supplied Accessories	AC plug holder (1)
Supplied Accessories	Cable holder (1)
Supplied Accessories	Bracket (1)
Supplied Accessories	Connection Cable for Color Temperature Probe (1)
Supplied Accessories	Operation Manual (Japanese, English, each 1)
Supplied Accessories	CD-ROM (1)
Supplied Accessories	Using the CD-ROM Manual (1)
Optional Accessories	BKM-16R Monitor Control Unit
Optional Accessories	BKM-37H Controller Attachment Stand
Optional Accessories	SMF-700 Monitor Interface Cable

General

Optional Accessories	BKM-220D SDI 4:2:2 Input Adaptor (with serial number 2100001 or higher)
Optional Accessories	BKM-227W NTSC/PAL Input Adaptor
Optional Accessories	BKM-229X Analog Component Input Adaptor (with serial number 2200001 or higher)
Optional Accessories	BKM-243HS HD/D1-SDI Input Adaptor (with serial number 2108355 or higher)
Optional Accessories	BKM-244CC HD/SD-SDI Closed Caption Adaptor
Optional Accessories	BKM-250TG 3G/HD/SD-SDI Input Adaptor (with serial number 7100001 or higher)

Notes

Note	[*1] The values for dimensions are approximate.
------	---



© 2004 - 2026 Sony Corporation. Все права защищены. Полное или частичное воспроизведение без письменного разрешения запрещено. Компания оставляет за собой право вносить изменения в характеристики и спецификации без уведомления. Указанные размеры и вес являются приблизительными. Все товарные знаки являются собственностью соответствующих владельцев.