

## BTA-801

### Portable Tuner Mount Adaptor



#### Overview

- Allows a WRR-855A/855B to be mounted on a Sony professional camcorder
- Supplies DC power from a camcorder to the WRR-855A/855B via an incorporated DC/DC converter

#### Specifications

##### Audio Section

Analog Output	XLR-3-11C type (x1)
---------------	---------------------

##### General

Power Requirements	DC 10 to 17 V (12 V nominal)
--------------------	------------------------------

Power Consumption	200 mA DC or less (at DC 7 V)
-------------------	-------------------------------

Operating Temperature	32°F to 122°F
-----------------------	---------------

Operating Temperature	0°C to 50°C
-----------------------	-------------

Storage/Transport Temperature	-4°F to +140°F
Storage/Transport Temperature	-20°C to +60°C
Dimensions *[1]	88 x 142.5 x 31.5 mm (W x H x D) (including projecting parts)
Dimensions *[1]	3 1/2 x 5 5/8 x 1 1/4 inches (W x H x D) (including projecting parts)
Mass	Approx. 6.3 oz
Mass	Approx. 180 g
Supplied Accessories	Operating Instructions (1)
Supplied Accessories	DC power cable (1)
Supplied Accessories	Betacam attachment kit (1 set):
Supplied Accessories	- Holder (1)
Supplied Accessories	- Bracket (1)
Supplied Accessories	- Binding head screws (M4 x 6) (2)
Supplied Accessories	- Binding head screws (M3 x 6) (2)

## Notes

\*[1] The values for dimensions are

Note

approximate.

---

## Gallery

