

CCFN-50

50 metre optical fibre hybrid cable with opticalCON connector



Overview

Used with the HXC-D70 multi-transmission studio camera system

Optical fibre transmission for CA-FB70 and HXCE-FB70. 50m length cable.

Power and optical fibre hybrid cable

Used with CCFN-JC1 coupler, doubles the distance between the HXC-D70 camera and the recording system.

Features

Power and optical fibre hybrid cable

Used with CCFN-JC1 coupler, doubles the distance between the HXC-D70 camera and the recording system.

Related products



CA-TX70

Цифровой триаксиальный адаптер для камеры HXC-D70



HXC-P70

Доступная и компактная системная Full HD/SD-камера с тремя 2/3-дюймовыми CMOS-сенсорами Exmor и оптоволоконным



HXC-FB80

Студийная цветная HD-камера с тремя 2/3-дюймовыми CMOS-матрицами Exmor™

кабелем для
прямого
соединения

Gallery

