

Wide-angle prime

Carl Zeiss Lens

A
mount

Fixed Focal
Length

SAL24F20Z

Distagon T* 24mm F2 ZA SSM

Exquisite wide-angle rendering captures the mood of any scene

35mm full frame



ED



RF



SSM

ZEISS



A mode, 1/320 sec., F2.0, -1.0 EV, ISO 100, Daylight white balance

- High resolution throughout the entire aperture range. Delicate gradation with excellent contrast.
- 19cm minimum focus distance lets you close in on details.

Wide-angle prime


Distagon T* 24mm F2 ZA SSM

Carl Zeiss Lens





Fixed Focal Length

SAL24F20Z



● Aspherical lens ● ED glass



35mm-equivalent focal length (APS-C) **36 mm**

Max. magnification **0.29 x**

Min. Focus **0.19 m**

Filter diameter **72 mm**

Dimensions (Dia x L) **78 x 76 mm**

Weight (approx.) **555 g**

Spatial frequency	R	T
10 line pairs / mm	— (solid orange)	- - - (dotted orange)
20 line pairs / mm	— (solid green)	- - - (dotted green)
40 line pairs / mm	— (solid blue)	- - - (dotted blue)

R: Radial values
T: Tangential values

35mm full frame



ED



RF

FHB

SSM

The icons

Recommended subject icons



Portrait



Snapshot



Indoor



Macro and
close-up



Macro and
Close-up
(Tele-macro)



Wildlife



Landscape



Night scene



Vehicle



Bird



Sports and action



Travel



Movie

Function icons



Circular aperture

Super



Super ED / ED glass

Advanced



Advanced aspherical / Aspherical lens

Nano AR Coating

Nano AR Coating

IF

Internal focusing

RF

Rear focusing

FHB ^{3 buttons} **FHB**

Focus hold button

FRL ^{Electronic} **FRL**

Focus range limiter

Auto Clutch

Auto clutch

ADI

ADI flash metering

SSM

SSM (Super Sonic wave Motor)

SAM

SAM (Smooth Autofocus Motor)

OSS

OSS (Optical SteadyShot)

Active Mode

OSS

OSS (Optical SteadyShot - Active Mode)

PZ

Power Zoom

SMO

Smooth Motion Optics