

VPLL-Z4015

VPL-F Serisi için 1,85-2,44
yanstma açs oran
sunan Projeksiyon Lensi*



Overview

1,85-2,44* yanstma açs oran sunan ksa odak
yaknlatrma lensi

* Güncel modeller için yaklak rakam

Specifications

Teknik Özellikler

Yanstma açs
oran

**VPL-FHZ120L, VPL-
FHZ90L:**

1,85:1 - 2,44:1

**VPL-FHZ700L, VPL-
FX500L, VPL-FH500L:**

2,06:1 - 2,72:1 (XGA modeli)

2,02:1 - 2,67:1 (WUXGA modeli)

Zum / Odak

Elektrikli / Elektrikli

**VPL-FHZ120L, VPL-
FHZ90L:**

Dikey: +/- %98 Yatay: +/- %51

Lens kaydrma	VPL-FHZ700L, VPL-FX500L, VPL-FH500L: Dikey: Yukar %109 - Aa %109 Yatay: Sa %57 - Sol %57 (WUXGA modeli) Dikey: Yukar %86 - Aa %86 Yatay: Sa %57 - Sol %57 (XGA modeli)
Açklk	f/2,20 ila 2,60
Ekran boyutu	40 inç - 600 inç
Boyutlar	Yaklak G 148 x Y 133 x D 231 mm (G 5 13/16 x Y 5 1/4 x D 9 3/32 inç)
Arlk	Yaklak 3,0 kg (6,6 lb)

Gallery

