

## VPL-GTZ270

4K SXRD laser projector with  
5,000 lumens light output and  
superb image quality



### Overview

#### **Thrilling pictures with 4K clarity for visitor attractions and entertainment applications**

From museums and galleries to planetariums and other visitor attractions, the VPL-GTZ270 laser projector impresses audiences with a powerful 5,000 lm light output for vibrant, high-contrast images bursting with rich color and 4K detail. And with whisper-quiet fan noise, it won't disturb your audience's enjoyment of the show. The long-lasting laser light source is combined with 4K SXRD panel technology to deliver crisply detailed native 4K images (4096 x 2160) with more than four times the resolution of Full HD.

Picture quality is further enhanced by Reality Creation upscaling, plus support for HDR (High Dynamic Range) and extended color space to take full advantage of today's premium 4K content — and tomorrow's.

The VPL-GTZ270 is particularly suitable for demanding multi-projection applications in 2D or 3D, with consistently homogeneous brightness that is a result of the laser light source.

The highly efficient laser light source is rated for a nominal 20,000 hours (up to 40,000 hrs in constant brightness mode), for virtually zero maintenance without the need for any lamp exchanges.

Long term reliability is assured further by dust-sealed optics.

Installers will also appreciate the projector's auto calibration, compatibility with leading AV room automation systems, and a robust chassis that can be installed at any angle for maximum flexibility.

## Features

### **Native 4K clarity with more than four times the resolution of Full HD**

Advanced SXRD panel technology featured in Sony's digital cinema projectors delivers native 4K (4096 x 2160) resolution images, with no artificial pixel enhancement. Every detail is wonderfully clear and natural, without jagged edges or visible pixels.

### **High brightness**

An impressive 5,000 lumens light output ensures punchy, high-brightness images that can be seen clearly in any environment. In constant brightness mode uniform brightness is maintained over the life of the laser light source - ideal for applications where several projectors are used together.

### **Super high contrast ratio**

The advance optical engine reduces internal light leakage, for spectacularly high contrast images with huge amounts of finely-rendered picture detail in dark shots

### **Supports HDR**

Take full advantage of the latest content produced with High Dynamic Range (HDR) for sharp contrast and more accurate detail, from searing highlights to richly detailed dark scenes.

### **Wide color space**

Videos and still images look more vivid and natural with support for an expanded color gamut, meeting DCI cinema projector

specifications and BT.2020 (emulated).

## **Reality Creation upscaling**

Lower resolution input signals are accurately upscaled to 4K pixel resolution by Sony's advanced Reality Creation engine: you won't see any individual pixels - just beautifully natural 4K images.

## **Picture presets for any content**

Nine calibrated presets optimize projected image quality for a wide range of content types including cinema, film, TV, photo, gaming and more.

## **Long-lasting laser light source**

Thanks to the highly efficient and reliable laser light source, audiences can enjoy startlingly clear 4K pictures, plus up to 20,000 hours\* uninterrupted operation (40,000 hours\* in constant brightness mode) with no lamp replacement - far longer than conventional lamp based projectors.

\*Depends on usage and environment.

## **Long lasting, low maintenance optics**

Lens, light source and all optical components are sealed against dust for dependable long-term operation.

## **Low transport delay**

Enjoy responsive, lag-free performance with low transport delay ideal for fast-moving content.

## **Color correction and color space adjustment**

Hue, Saturation, Brightness and color space can be adjusted to suit different installation conditions.

## **Quick start**

Don't lose time - laser light source starts instantly, allowing you to start projecting in moments without lengthy lamp warm-up time.

### **Motionflow for smoother 4K images**

Motionflow ensures smoother, less blurry on-screen images.

### **Greater installation flexibility**

Install the projector horizontally, vertically, upside down or at any angle with no restrictions. The rugged chassis allows projectors to be stacked directly on top of one another. Projectors can also be stacked side by side with no cabling restrictions.

### **Auto calibration**

Auto calibration adjusts RGB color levels as well as white point over the lifespan of the laser light source for consistently beautiful images over time.

### **Industry standard RF 3D compatible**

The projector's built-in RF transmitter synchronizes with any RF 3D glasses for wider coverage and greater stability, with no need for an external transmitter.

### **Whisper quiet operation**

Extra-low noise fan with one-way air flow and liquid cooling system ensures extra-quiet operation for minimized audience disruption. High altitude mode adjusts fan rate for efficient operation at altitudes above 1500m.

## Specifications

### Display System

Display System	4K SXR panel, projection system
----------------	---------------------------------

### Display device

Size of effective display area	0.74" x 3
--------------------------------	-----------

Number of pixels	26,542,080 (4096 x 2160 x 3) pixels
------------------	-------------------------------------

---

## Projection lens\*2

Focus	Powered
-------	---------

---

Zoom	Powered
------	---------

---

## Light Source

Light Source	Laser diode
--------------	-------------

---

## Light Output

Light Output	5,000 lm
--------------	----------

---

## Color Light Output

Color Light Output	5,000 lm
--------------------	----------

---

## Contrast ratio

Dynamic	Up to 30,000:1*1
---------	------------------

---

Native	Up to 20,000:1*1
--------	------------------

---

## Accepted digital signals\*3

VGA, SVGA, XGA, WXGA (1280x768),

---

Accepted digital signals*3	Quad-VGA, SXGA, 720x480/60p, 720x576/50p, 1280x720/50p, 1280x720/60p, 1920x1080/50i*4, 1920x1080/60i*4, 1920x1080/24p, 1920x1080/50p, 1920x1080/60p, 3840x2160/24p, 3840x2160/25p*4, 3840x2160/30p*4, 3840x2160/50p, 3840x2160/60p, 4096x2160/24p, 4096x2160/25p*4, 4096x2160/30p*4, 4096x2160/50p, 4096x2160/60p
----------------------------	--

## Color bit depth

Color bit depth	Up to 12 bit via HDMI / Up to 10 bit via Display Port
-----------------	---

## INPUT OUTPUT (Computer/Video/ Control)

HDMI	2 inputs (HDCP 2.2 x 2), Digital (RGB/Y Pb/Cb Pr/Cr)
Display Port	2 inputs (HDCP 1.3 x 1, HDCP 1.3 for V Split x 1), Digital (RGB)
TRIGGER	2 connectors, Mini jack, DC 12V Max.100 mA
REMOTE	RS-232C, D-sub 9-pin (female)

---

LAN	RJ45, 10BASE-T/100BASE-TX
IR IN / OUT	IN:1, Out:1 , Mini jack
SYNC	Not available
USB	Type A

---

## OSD languages

OSD languages	18-languages (English, Dutch, French, Italian, German, Spanish, Portuguese, Turkish, Russian, Swedish, Norwegian, Japanese, Simplified Chinese, Traditional Chinese, Korean, Thai, Arabic, Polish)
---------------	--

---

## Acoustic noise

Acoustic noise	30 dB ~ 35 dB*1
----------------	-----------------

---

## Operating temperature / Operating humidity

Operating temperature / Operating humidity	5°C to 40°C (41°F to +104°F)/20% to 80% (no condensation)
---	--

---

## Storage temperature / Storage humidity

---

Storage temperature / Storage humidity	-10°C to + 60°C (14°F to +140°F)/20% to 80% (no condensation)
---	---

---

## Power requirements

Power requirements	AC 220 V to 240 V, 6 A, 50/60 Hz (For Europe and China)
Power requirements	AC 100 V to 240 V, 12 A to 6 A, 50/60 Hz (For the other countries)

---

## Power consumption

Power consumption	MAX. 1.2 kW
Power consumption (Standby Mode)	0.4 W (When “Remote Start” is set to “Off”)
Power consumption (Networked Standby Mode)	0.6 W (LAN) (When “Remote Start” is set to “On”)

---

## Heat dissipation

Heat dissipation	4092 BTU/h
------------------	------------

---

## Dimensions (W x H x D)



Dimensions (W x H x D) 550 x 228 x 750 mm  
 (21 21/32 x 8 31/32 x 29 17/32 in)  
 (without protrusions) 550 x 262 x  
 750 mm  
 (21 21/32 x 10 5/16 x 29 17/32 in)

## Mass

Mass Approx. 40 kg / 88 lb (excluding lens)

## Supplied accessories

Supplied accessories RM-PJ29 Remote Commander (1),  
 Size AA (R6) Manganese Batteries  
 (2),  
 AC Power Cord (1),  
 Operating Instructions (CD-ROM)  
 (1)

## Notes

\*1 This value is approximate.  
 Depends on the projector setting  
 condition and usage environment.

\*2 The lenses are optional  
 accessories.

\*3 60p,30p,24p include 59.94/60Hz,  
29.97Hz/30Hz, 23.98Hz/24Hz

---

\*4 Available via HDMI input

---

## Gallery

