

B4S16PLKIT

Kit including B4S16PL & LAFZPL12P adapters for use of 2/3-inch lenses with PMW-F5/F55 (Center Scan).



Overview

Kit including B4S16PL & LAFZPL12P adapters for use of 2/3-inch lenses with PMW-F5/F55 (Center Scan).

Highlights

- 2/3-inch "B4" lens & PL adapter kit for use with PMW-F5/F55 cameras
- Low light loss, less than one Stop loss (passes about 80% of the light).
- Lens user interface is fully supported: Zoom, REC button etc. (Return is assignable).
- Lens Iris, Zoom & Focus metadata is displayed on the viewfinder, it is also recorded and output over SDI via SMPTE RDD18 protocol.

Specifications

Supplied Accessories

	B4 Body cap
Supplied Accessories	Black FZ ring for PMW-F5 Silver FZ ring for PMW-F55

Gallery

