

C-100

Two Way Condenser Microphone



Overview

The Sony C-100 is a two way condenser microphone, compatible with High-Resolution Audio, and suitable for vocal and critical instrument recording in the studio. Incorporating newly developed double microphone capsules and noise elimination structure, originally employed in the C-800G microphone, the C-100 delivers a broad frequency range of 20 to 50,000 Hz and excellent reproduction of vocal and musical qualities. The condenser element of the C-100 microphone provides a selectable pick-up pattern (Omni/Uni/Bi) for various recording applications.

Features

Excellent Sound Quality

Two-way microphone capsule structure realizes both broad high range and resonant mid-low range and gives great vocal presence.

Wide Frequency Response

The C-100 microphone has a broad frequency response (20 Hz to 50kHz) and provides superb sound reproduction quality for High-Resolution Audio.

Noise Elimination Construction

Two-part metallic body structure succeeded from C-800G microphone prevents acoustic vibration resulting in low noise and clear sound.

Switchable Polar Patterns

The C-100 microphone features switchable uni-directional, omni-directional and Figure-8 polar patterns for various recording applications.

Low-Cut Filter

Low-Cut filter switch helps eliminate low-frequency noise and proximity effect.

Pad Switch

An -10dB pad switch on C-100 microphone provides added headroom and minimizes distortion caused by transient peaks.

Specifications

Audio Section

Capsule Type	2 Way Microphone (Condenser + Back electret condenser)
Frequency Response	20 Hz to 50 kHz
Directivity	Uni-directional/Omni-directional/Bi-directional
Sensitivity *[1]	(Uni-directional) -31 dB (Omni-directional) -37 dB (Bi-directional) -35 dB

Audio Section

Output Impedance *[2]	90Ω±15%, Balanced
Dynamic Range	(Uni-directional) 113 dB or more (Omni-directional) 114 dB or more (Bi-directional) 114 dB or more
Signal-to-Noise Ratio *[3]	(Uni-directional) 75 dB or more (Omni-directional) 70 dB or more (Bi-directional) 72 dB or more
Inherent Noise *[4]	(Uni-directional) 19 dB SPL or less (Omni-directional) 24 dB SPL or less (Bi-directional) 22 dB SPL or less
Maximum Input Sound Pressure Level *[5]	(Uni-directional) 132 dB SPL (Omni-directional) 138 dB SPL (Bi-directional) 136 dB or SPL

General Section

Connector	XLR-3-12C (male)
Mic Cable	XLR 3-pin Cable Required (Not Supplied)
Power Requirements	DC 44 to 52 V
Dimensions *[6]	40dia.×175mm (1.57dia.×6.89in.)
Mass	Approx. 290g (10.2oz.)
Supplied Accessories	Cradle suspension (1) Wind screen (1) Stand screw adaptor (W3/8 to NS5/8) (1) Operating instructions (1) Carrying case (1)

Notes

*[1]	0 dB = 1 V/Pa, at 1 kHz
*[2]	Output impedance at 1 kHz
*[3]	A-weighted, 1 kHz, 1 Pa.
*[4]	0dB SPL = 20μPa.
*[5]	0 dB SPL = 20μPa.
*[6]	The values for dimensions are approximate.

Related products



C800GPAC

Studio Tube Condenser
Microphone PAC



C-80


Uni-directional Condenser
Microphone



C-800GPAC1

Studio Tube Condenser
Microphone PAC

Gallery



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.