

CBK-3610XS

VENICE Extension System



Overview

Unparalleled flexibility with uncompromised image quality

The VENICE Extension System (CBK-3610XS) enables cabled separation of the VENICE camera body and image sensor block by up to 18 ft with no degradation in image quality.

The kit consists of a front panel cover, image sensor block case, and a 2.7 m (9 ft) cable with an additional 2.7 m (9 ft) extension cable. (VENICE camera is not included.)

The Extension System also has an HD-SDI output and a 24 V output for powering accessories such as lens servo motors and monitoring. Multiple screw holes on all surfaces make it easy to affix additional accessories and fit with a wide variety of rigs. The Extension System is fully compatible with all existing and future VENICE cameras upgraded to V3 or higher firmware.

The Extension System is fully compatible with VENICE and VENICE 2 camera systems with 6K imager block. New kit supporting 8K imager block is planned for future release.

Features

Enhanced mobility and maneuverability

Separation of the camera body and image sensor block of up to

5.5 m enables exceptional flexibility when filming with gimbals, handheld, in helicopter/underwater housings, with custom rigs such as those used for 3D/VR content, and shooting scenes in confined spaces such as vehicles. The separated image block weighs just 4 lb (1.9 kg) with PL mount and 3 lb (1.4 kg) with e-mount for the utmost shooting flexibility.

Uncompromised image quality

When shooting with CBK-3610XS there's no degradation in image quality. Whether shooting with a standard 2.7 m separation or using the extension cable for a maximum 5.5 m separation, you can be sure the image quality is the same as shooting with VENICE in standard configuration.

Advanced Features

CBK-3610XS preserves full use of the advanced features VENICE offers, such as its built-in 8-step glass ND filter system, Dual Base ISO, and more.

Specifications

General	
Power Consumption	Approx. 2.4 W (with 8.86 ft extension) Approx. 3.9 W (with 18.05 ft extension)
Operating Temperature	0 °C to 40 °C (32 °F to 104 °F)
Storage Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Mass	

CBK-3610XS	Approx. 2.9 kg (6.40 lb) (excluding supplied accessories)
Imager Block to be Installed to CBK-3610XS	with PL Mount: Approx. 1.9 kg (4.19 lb) with E Mount: Approx. 1.4 kg (3.09 lb)
Input/Output Connectors	24 V IN connector (Fischer 3-pin) (1) 24 V OUT connector (Fischer 3-pin) (1) MONITOR IN connector (BNC type) (1) MONITOR OUT connector (BNC type) (1)

Related products



CBK-3620XS

VENICE Extension System 2

Gallery

