

CCFN-50

50 meter optical fiber hybrid cable with opticalCON connector



Overview

Used with the HXC-D70 multi-transmission studio camera system

Optical fiber transmission for CA-FB70 and HXCE-FB70. 50m length cable.

Power and optical fiber hybrid cable

Used with CCFN-JC1 coupler, doubles the distance between the HXC-D70 camera and the recording system.

Features

Power and optical fiber hybrid cable

Used with CCFN-JC1 coupler, doubles the distance between the HXC-D70 camera and the recording system.

Related products



CA-FB70

Fiber adapter for HXC-D70 and PMW-320/350/400/500 camcorders



CA-TX70

Digital triax adapter for HXC-D70



HXC-P70

Affordable, three 2/3-inch Exmor CMOS sensor, full HD/SD compact system camera with direct optical fiber cable connection



HXC-FB80

Three 2/3-inch Exmor™ CMOS sensor HD color studio camera

Gallery

