

EC0-5X5F3M

5-pin to Dual 3-pin XLR Cable for ECM-680S. Formally known as K-1504



Overview

5-pin to Dual 3-pin XLR Cable for ECM-680S. Formally known as K-1504

Formally known as K-1504. Short cable used to connect ECM-680S stereo shotgun mic (5-pin XLR output) to a camcorder. This 16" length short cable is intended to be used for mounting the ECM-680S onto a camcorder that is fitted with two 3-pin XLR mono mic inputs.

Highlights

- Formally known as K-1504
- 5-pin female XLR on one end - two 3-pin male XLR's on the other end
- Cable length 16"

Gallery

