

LMD-2110W

21.5-inch entry-level LCD monitor



Overview

Affordable high picture performance

The LMD-2110W is an elegant 21.5-inch widescreen LCD monitor specifically designed to provide reference video monitoring solution for entry-level video applications.

Its 21.5-inch size and Full HD (1920x1080) picture resolution makes this video monitor ideal in various applications such as entry-level non linear editing, videographer, high definition office viewing, security and medical, and some others.

A 10-bit processor ensures accurate picture reproduction will less image artifacts. Combined with a high purity filter, the LMD-2110W provides excellent color depth for precise color reproduction.

Equipped with a HDMI interface as standard, this new entry-level monitor is an ideal match for professional and semi-professional high-definition applications. This monitor can be used for desktop editing and office viewing applications with video or computer format input through DVI to HDMI conversion cable.

The LMD-2110W also supports both HD-SDI and SD-SDI with the optional BKM-341HS adaptor.

The LMD-2110W wins hands-down in terms of breadth of operation and performance when compared to standard PC monitors: - video image reproduction is far superior due to its moving picture optimisation circuitry and color temperature and Gamma control.

Slim and lightweight, the LMD-2110W also offers outstanding installation flexibility. It has a table stand and VESA mount as standard enabling it to be easily placed on a desktop, in a monitor wall or on a ceiling.

Entirely at home in many professional environments, the LMD-2110W truly redefines high performance in the entry-level sector.

Suitable for a Wide Range of Applications

Ideal for many entry-level applications from office viewing and monitor wall in Broadcast and corporate environments, desktop monitor for non linear editing, reference video monitor for videographers, security and medical as well.

Cost-Effective Feature-Rich Performance

The LMD-2110W offers professional functionality in an economic package. Optimized for moving picture reproduction, it delivers accurate color rendition and grayscale – thanks to its CRT-like gamma curve. And it sports a wide range of video interfaces and professional features allowing confident video signal evaluation.

Superb High Resolution Display

Equipped with a 16:9 Widescreen 1920x1080 LCD panel it delivers outstandingly sharp high brightness and contrast pictures

Comprehensive High-Definition Capability via HDMI input

HDMI offers access to uncompressed digital video and audio signals. The range of applications using these connectors is

expanding and HDMI is increasingly being employed.

Future Proof

Multi-format and HDMI capability ensures that the LMD-2110W remains current.

Consistently Optimal Picture Performance

Less 'drift' than CRT displays, with no convergence, geometry or linearity issues, and no susceptibility to magnetic fields.

Exceptionally Versatile

Equally suited to AV or IT-based applications due to a broad range of inputs and multi-format signal capabilities.

Easier to Install and Accommodate than CRT

Space saving / lightweight / low heat output.

Low Maintenance

No routine convergence, geometry or purity adjustments necessary. No susceptibility to magnetic fields.

Reduced Operator Fatigue

Flicker-free picture is more comfortable to view and reduces eye-strain.

Lower Total Cost of Ownership than CRT

Simpler and cheaper to install, transport and store.

Long operational life / high reliability.

Low energy bills.

Low maintenance cost.

Reduced environmental disposal costs.

Features

Full HD-resolution (1920 x 1080) LCD panel

Delivers outstandingly crisp, high brightness and high contrast widescreen HD images with a fast transient response.

Cost-Effective Feature-Rich Performance

The LMD-2110W offers professional functionality in an economic package. Optimized for moving picture reproduction, it delivers accurate color rendition and grayscale – thanks to its CRT-like gamma curve. And it sports a wide range of video interfaces and professional features allowing confident video signal evaluation.

High-purity Color Filter

The LMD-2110W monitor provides high-brightness, high-contrast images thanks to its wide aperture LCD panel. In addition, the use of precisely manufactured RGB color filter allows this monitor to reproduce colors with stunning depth and saturation - creating highly natural images.

109% Peak White and 10-bit Signal Processing

Incorporating high-purity RGB color filter and a 10-bit signal processing engine, the LMD-2110W monitor offers stunning 109% peak white reproduction without clipping and a smooth gray scale along CRT-like gamma.

Minimized Picture Delay

Picture delay can be minimized for audio synchronization. Selecting LINE DOUBLER in I/P mode, the signal processing (I/P conversion) period is less than one field (0.5 frames).

Input Versatility

The LMD-2110W is equipped with a full range of analog SD inputs including composite NTSC/PAL, Y/C (S-Video), 525i/625i component, and RGB. This monitor can also handle SD-SDI input using an optional BKM-320D SD-SDI input adaptor. Furthermore, it offers an HD signal input capability via the HDMI and analog component interface.

Optional HD/SD-SDI input

With the BKM-341HS optional adaptor, the LMD-2110W supports both HD-SDI and SD-SDI input, with a higher picture quality and shorter depth compared to the BKM-320D SD-SDI input adaptor.

Multi-Format Signal Support

Includes NTSC, PAL, component, RGB, Y/C, 480/60i, 575/50i, 480/60p, 576/50p, 1080/50i, 1080/60i, 720/50p, 720/60p, 1080/24psf, 1080/25psf, 1080/24p, 1080/25p and 1080/30p. The LMD-2110W also accepts standard definition digital signals with an optional SD-SDI input adaptor.

HDMI input for High Definition Display

Increasingly an interface of choice for entry-level production.

Color Temperature Adjustment

D65, D93 or user presets can be selected.

CRT-like Gamma Curve

For accurate grayscale performance.

Selectable Scan Size and Aspect Ratio

Normal scan (0%), Over-scan (5%) and Full scan is available. Also, aspect ratio can be switched between 16:9 and 4:3.

Three Color Tally

The tally lamp can be lit via a parallel remote connector and status identified by three colors: red, green or amber.

Video Markers

Equipped with a central marker plus 4:3 and 16:9 markers for Over-scan and Normal-scan display.

Blue Only Mode

In the blue only mode, a monochrome display is shown. This mode is convenient for chroma and phase adjustments and monitoring of signal noise.

Remote Control

Via a programmable parallel remote interface.

Mono Audio Monitoring

The LMD-2110W is equipped with a mono speaker.

VESA Mounting (100x100mm)

Desktop or simple wall / ceiling mounting.

19-inch Rack Mountable kit

With optional MB-529 fixing kit.

External Sync

The unit can be operated on the sync signal supplied from an external sync generator.

Specifications

Picture Performance

Panel	a-Si TFT Active Matrix LCD
Picture Size (Diagonal)	547 mm 21 5/8 inches
Effective Picture Size (H x V)	447.0 x 268.0 mm 18 7/8 x 10 5/8 inches
Resolution (H x V)	1920 x 1080 pixels (Full HD)
Aspect	16:9
Pixel Efficiency	0.9999
Colors	Approx.16.7 million colors

Viewing Angle (Panel Specification)	80°/80°/85°/85° (typical) (up/down/left/right contrast 10:1)
-------------------------------------	---

Input

Composite Input	BNC (x1), 1 Vp-p \pm 3dB, negative synchronization
Y/C Input	Mini DIN 4-pin (x1) Y: 1 Vp-p \pm 3dB sync negative C: 0.286 Vp-p \pm 3dB (NTSC burst signal level), 0.3 Vp-p \pm 3dB (PAL burst signal level)
RGB, Component Input	BNC (x3) RGB: 0.7 Vp-p \pm 3dB (Sync On Green, 0.3 Vp-p negative sync.) Component: 0.7 Vp-p \pm 3dB (75% chrominance standard color bar signal)
HDMI Input	HDMI (x1) (HDCP correspondence)
Audio Input	Phono jack (x2), -5 dBu 47 k Ω or higher
External Sync Input	BNC (x1), 0.3 to 4.0 Vp-p negative polarity binary
Option Input	D-sub 9-pin (x1), female

Parallel Remote	Modular connector 8-pin (x1) (Pin-assignable)
-----------------	--

Output

Composite Output	BNC (x1), Loop-through, with 75 Ω automatic terminal function
------------------	---

Y/C Output	Mini DIN 4-pin (x1), Loop-through, with 75 Ω automatic terminal function
------------	---

RGB, Component Output	BNC (x3), Loop-through, with 75 Ω automatic terminal function
--------------------------	---

External Sync Output	BNC (x1), Loop-through, with 75 Ω automatic terminal function
----------------------	---

Audio Monitor Output	Phono jack (x2) , Loop-through
----------------------	--------------------------------

Speaker (Built-in) Output	0.5 W (mono)
------------------------------	--------------

General

Power Requirements	100 V to 240 V AC, 1.3 A to 0.6 A, 50/60 Hz
--------------------	--

Power Consumption	Approx. 69 W (max.)
-------------------	---------------------

(1) Maximum possible

Inrush Current	<p>inrush current at initial switch-on (Voltage changes caused by manual switching): 60A peak, 0.4A r.m.s. (240V AC)</p> <p>(2) Inrush current after a mains interruption of five seconds (Voltage changes caused at zero-crossing): 48A peak, 0.3A r.m.s. (240V AC)</p>
Operating Temperature	<p>0°C to 35°C (Recommended: 20°C to 30°C)</p> <p>32°F to 95°F (Recommended: 68°F to 86°F)</p>
Operating Humidity	30% to 85% (no condensation)
Storage/Transport Temperature	<p>-20°C to +60°C</p> <p>-4°F to +140°F</p>
Storage/Transport Humidity	0% to 90%
Operating/Storage/Transport Pressure	700 hPa to 1060 hPa

Dimensions (W x H x D) [*1]	515.0 x 355.0 x 86.0 mm (without a stand) 515.0 x 403.0 x 264.0 mm (with a supplied stand) 20 3/8 x 14 x 3 1/2 inches (without a stand) 20 3/8 x 15 7/8 x 10 1/2 inches (with a supplied stand)
Mass	Approx. 8.6 kg Approx. 18 lb 15 oz
Supplied Accessories	AC power cord (1) AC plug holder (1) Operating Instructions (1) CD-ROM (1) Using the CD-ROM Manual (1)
Optional Accessories	MB-529 Mounting Bracket BKM-320D SDI Input Adaptor BKM-341HS HD/SD-SDI Input Adaptor

Notes

Note [*1] The values for dimensions are

approximate.

Environmental notice
for customers in the
USA

Lamp in this product contains mercury. Disposal of these materials may be regulated due to environmental considerations. For disposal or recycling information, please contact your local authorities or see www.sony.com/mercury for additional information. No Hg (mercury) contained due to change LED backlight from Serial Number 3200001.

Related products



MCS-8M

Compact SD / HD audio and video switcher



HXR-NX100

1.0-type Exmor R™ CMOS Sensor NXCAM camcorder with maximum 48x zoom lens and 3 independent manual lens rings recording XAVC S, AVCHD and DV



HXR-NX5R

Three 1/2.8-inch Exmor CMOS sensors Full HD AVCHD / XAVC S camcorder with 40x zoom with Clear Image Zoom and built-in wireless functionality.

Gallery

