

## PDT-FP1

Portable data transmitter with 5G, mmwave and sub6 for high-speed transmission of video and still images



### Specifications

General	
Dimension	Approx. 170.0 mm x 80.0 mm x 26.6 mm (HxWxD) Approx. 6.7 inch x 3.2 inch x 1.1 inch (HxWxD)
Weight	Approx. 308 g Approx. 10.9 oz.
OS	Android™ 13*1
CPU	Snapdragon® 8 Gen 2 Mobile Platform*2
Internal memory (RAM/ROM)	8 GB/256 GB*3
External memory	Up to 1 TB (microSD/microSDHC/microSDXC)*4*5
Battery	Lithium-ion battery (5000 mAh)

2D Code Scanner	Yes
SIM type	nanoSIM/eSIM*6
Dual SIM specification	DSDS
Bluetooth	Bluetooth® 5.3 wireless technology
Display	OLED (1080 x 2520), 6.1 inch
Speaker	Yes
GPS	A-GPS, A-GLONASS, Beidou, Galileo, QZSS*7

## Network

Wi-Fi®	IEEE802.11a/b/g/n/ac/ax, 2.4/5/6 GHz*7
Wi-Fi tethering max. number of clients	Up to 10 devices
LTE Band	1, 2, 3, 4, 5, 7, 8, 11, 12, 13, 17, 18, 19, 20, 21, 25, 26, 28, 29, 30, 32, 34, 38, 39, 40, 41, 42, 46, 48, 66, 71*8
5G (Sub6) Band	NSA: n1, n2, n3, n5, n7, n8, n20, n25, n28, n30, n38, n40, n41, n66, n71, n77, n78, n79*8 SA: n1, n2, n3, n5, n7, n8, n20, n25,

n28, n38, n40, n41, n48, n66, n71,  
n77, n78, n79\*8

5G (mmWave) Band n257, n258, n260, n261\*8

Maximum throughput (5G) Uplink: Up to 1.1 Gbps/Downlink:  
Up to 8.1 Gbps\*9\*10

## Input interface

USB Type-C® terminal (Data transfer) USB Type-C® (SuperSpeed USB  
5 Gbps (USB3.2))

USB Type-C® terminal (CHARGE) USB Type-C®

HDMI® connector Type-A: [YCbCr 4:4:4 / 4:2:2 / RGB]  
3840 x 2160  
(60p/50p/30p/25p/24p), 1920 x  
1080 (60p/50p/30p/25p/24p), 1280  
x 720(60p/50p/30p/25p/24p), 720 x  
480 (60p), 720 x 576 (50p), 640 x 480  
(60p)\*11

LAN terminal 10BASE-T, 100BASE-TX, 1000BASE-  
T

## Cooling fan

Type DC FAN

Thickness of fan	Approx. 5.0 mm (Approx. 0.2 inch)
------------------	-----------------------------------

Air flow	Approx. 51 L/min*12
----------	---------------------

## Heat sync

Size	Approx. 37.15 mm x 19.3 mm x 7.3 mm (Approx. 1.5 inch x 0.8 inch x 0.3 inch)
------	--

## Power

Power delivery	Yes (USB Power Delivery)*13
----------------	-----------------------------

Charging time	Approx. 115 minutes*14*15
---------------	---------------------------

Operating time (FTP transfer via USB in LTE)	Approx. 4 hours*16*17
--	-----------------------

Operating time (Video upload via HDMI)	Approx. 2 hours*17*18
--	-----------------------

Standby time (LTE)	Approx. 600 hours*17*19
--------------------	-------------------------

Standby time (5G SA)	Approx. 450 hours*17*19
----------------------	-------------------------

## Operating Temperature

Operating

Temperature 0 - 40 °C / 32 - 104 °F

---

## Supplied Accessory

Supplied Accessory -

---

## Accessibility

Accessibility

Select to Speak, TalkBack, Text-to-speech output, Font size, Display size, Dark theme, Magnification, Color correction, Color inversion, Large mouse pointer, Remove animations, Accessibility Menu, Switch Access, Click after mouse pointer stops moving, Auto-rotate screen, Touch & hold delay, Time to take action (Accessibility timeout), Vibration & haptic strength, System navigation, Mono audio, Audio balance, Caption preferences, High-contrast text, Shortcut from lock screen

---

## Notes

\*1 Android™ is a trademark of Google LLC.

---

\*2 Qualcomm and Snapdragon are trademarks of Qualcomm Incorporated, registered in the United States and other countries and regions.

---

\*3 Firmware and preloaded applications take up a portion of internal storage, with the remainder available for user-selected content. Measurement made at time of product announcement and may vary per market. As software updates may change the available internal storage, internal memory may vary depending on market.

---

\*4 Sold separately.

---

\*5 microSD, microSD logo and microSDHC logo are trademarks of SD-3C LLC.

---

\*6 eSIM service availability and condition may vary depending on the countries, regions and carrier.

---

\*7 This service is not available in all variants or markets.

---

\*8 Availability may vary depending on countries/regions, carrier, software version and user environment.

---

\*9 Theoretical value. Performance is subject to environment and conditions.

---

\*10 Actual throughput depends on network condition.

---

\*11 Use of a Premium High-Speed HDMI Cable with Ethernet manufactured by Sony is recommended.

---

\*12 Measured values in Sony measurement environment.

---

\*13 Use of Sony-designed chargers and cables is recommended.

---

\*14 When charging with the optional AC adapter (XQZ-UC1) supporting 30 W quick charge.

---

Charging time depends on settings

---

\*15 and environmental conditions, and actual results may vary.

---

\*16 When using Transfer & Tagging app for file transfer. Sony measurement.

---

\*17 Operating time depends on settings and environmental conditions, and actual results may vary.

---

\*18 When using an external monitor app for video upstreaming. Sony measurement.

---

\*19 Measured based on GSMA TS.09 operating time measurement method (Ver.12.0). Sony measurement.

---

## Related products



### **PXW-Z280**

World's first 4K Handheld Camcorder with 1/2-type 3CMOS with 4K 50p/60p recording capability, 12G-SDI, Dual Link Cellular capability, 17x zoom lens, advanced



### **PXW-Z750**

4K 2/3-type 3-chip CMOS Shoulder-mount Camcorder with global shutter, high sensitivity, 4K/HD simultaneous recording, 120p HFR in HD, 12G-SDI and



Face Detection AF

advanced wireless  
workflow capabilities.

## Gallery



