

RCP-3501

Remote-control panel for
HDC/HSC/HXC series cameras



NETWORKED **LIVE**

Overview

The RCP-3501 is the successor model for RCP-1501 while keeping the same dimensions and the same basic functions

The RCP-3501 remote-control panel incorporates direct operation switches and a touch panel, and offers improved visibility with a higher-resolution and brighter LCD display. These factors make it a remote-control panel that offers both ease of operation and multi-functionality that compares favorably with the MSU. The iris and master black adjustment block employs dial type control. Up to four units can be mounted in a 19-inch EIA rack.

Features

Touch panel and many direct access switches suitable for various camera operations

This remote-control panel is equipped with the control functions required to perform various camera operations, enabling simple and accurate operation. The operation buttons, adjustment knobs, and other controls are arranged on the panel according to function and frequency of use. Guard frames are provided around buttons that are vital for camera operation and setup, in order to prevent the buttons from being unintentionally operated.

Assignable keys

The RCP-3501 has 9 keys assigned with a variety of functions. A spare LED can be also assigned to indicate functioning. All the assigned buttons and LED can be listed on the display for easy understanding at a glance.

LAN connection capability

It is possible to connect it using a LAN cable, in addition to a CCA-5 cable. The system can be built using a 1000Base-T LAN connection with PoE support.

Customizable switches

Users can assign any function to the 9 assignable buttons and also make their own favorite menu as well. This is available via SW Customize menu with the categorized items.

HDR operation support

The RCP-3501 supports the HDR-related File Names of "All-Setting-File" of HDRC-4000 that can be organized on the RCP's display panel.

The SR Live MetaFile is also supported with HDRC-4000 to link the HDR metadata in addition to SDI connection path.

USB flash drive

The RCP's settings can be saved or loaded via USB flash drive. CAM/CCU/BPU Scene files/Reference files can also be saved, and for the HDRC-4000's HDR Production Converter Unit the All Setting file can be saved.

Direct Scene file control

Easily access Scene file to support various scene setting.

Web UI application

Allows convenient remote operation for RCP initial settings from a remote networked PC with intuitive user interface (UI).*

*Feature available at a later date.

Specifications

General

Power supply	DC 10.5 V to 17 V (for EXT I/O connector) PoE 36 V to 57 V (IEEE802.3af class 2-compliant)
Power consumption	10 W (including AUX connector output)
Operating temperature	5 °C to 40 °C (41 °F to 104 °F)
Storage temperature	-20 °C to 60 °C (-4 °F to 140 °F)
Dimensions (W x H x D)	102 x 310 x 67 mm (4.02 x 12.20 x 2.64 inches) (excluding protrusions)
Mass	1.7 kg (3 lb 12 oz)

Input/Output Connectors

LAN	RJ-45 8-pin (x1) 1000BASE-T, 100BASE-TX, 10BASE-T
CCU/CNU	Multi-connector 8-pin, female (x1)
AUX	Multi-connector 8-pin, female (x1)
EXT I/O	D-sub 9-pin, female (x1)

Related products



BRC-H800

Premium Full HD PTZ Camera with 12x optical zoom and uncompromising broadcast picture quality



CNA-1

Camera control network adaptor



BRC-X1000

Premium 4K30P PTZ Camera with 12x optical zoom and uncompromising broadcast picture quality



HDC-P31

HD compact POV system camera with enhanced remote features and advanced HDR workflows



UHC-8300

UHC-8300 8K 3CMOS sensor Camera system includes UHCU-8300 8K Camera Control Unit, UKCU-8001 (8K ST 2110 Interface), UZCU-SNMP80 (SNMP for 8K ST 2110), UKCU-IP01F (Networked Media Interface)



HDCU-3100

IP-enabled next-generation Camera Control Unit



HDCU-3170

IP capable Triax Camera Control Unit



HDCU-3500

IP-ready Camera Control Unit (CCU) for HDC-3500 4K/HD system camera



HDCU-5000

Camera Control Unit (CCU) for HDC-5500 and HDC-3500/3100 series system cameras



HDCU-5500

IP-ready Camera Control Unit (CCU) for HDC-5500 4K/HD system camera



HDC-P50

4K/HD compact POV system camera



HXCU-FB80

4K / HD Camera Control Unit for HXC-FB80 cameras



HXC-P70



BRC-X400



MSU-3000



MSU-3500

Affordable, three 2/3-inch Exmor CMOS sensor, full HD/SD compact system camera with direct optical fiber cable connection



HDRC-4000

HDR Production Converter Unit

Premium 4K30P IP PTZ Camera with 30x (w/CIZ) zoom and NDI®|HX capability for use in a wide range of environments



HDC-F5500

Super 35-mm 4K CMOS Camera System

Master setup unit, multi-camera remote control panel for system cameras (horizontal type)

Master setup unit, multi-camera remote control panel for system cameras (vertical type)

Gallery

