

## RM-30BP

### Remote Commander



### Overview

The RM-30BP is the successor to the RM-1000BP, the industry's first comprehensive, multifunctional remote commander.

Ideal for freelancers and small-budget productions, the lightweight remote can be handheld, placed on a table, or attached to a tripod arm for operation. The RM-30BP can control most camera functions including:

- Lens control: one push auto/manual focus, iris, and zoom control
- Camera control: recording/display functions, shutter speed, white balance—including six assignable buttons
- Playback and multi camera control (up to 3 cameras)

The RM-30BP is compatible with a wide range of Sony camcorders, including PXW-FX9 and ILME-FX6. Please consult the Resources section for the latest Compatibility Notes PDF.

### Specifications

#### Notes

Specifications are tentative and subject to change.

## Specifications

Dimensions (Approx.)	82.5 x 34 x 174.5mm (W x H x D) Except for the maximum protrusion
Weight (Approx.)	290g (Body only)
Operating temperature	0°C~+40°C
Storage temperature	-20°C~+60°C
Power consumption	0.2W below
Power-supply voltage	4.2~6.0 v ; supplied from Camcorders
Input/Output	CAMERA x3 / 2.5mm TRS Plug REMOTE x1 / 2.5mm TRS Jack OPTION x1 / 3.5mm TRS Jack

## Gallery

