

SxS PRO X Memory Card

120 GB, 240 GB SxS PRO X Series Memory Card



Overview

Ultra-Fast Transfer Speed up to 10 Gps (1,250 MB/s)*

Using the PCI Express 3.0 advanced interface and Sony's newly developed unique intelligent controller delivers 3 x faster ingest time compared to current versions. In combination with the new SBAC-T40 reader/writer, the PRO X transfers 240-GB video content to a computer in approximately 3.5 minutes, which greatly improves workflow efficiency for professionals.

*Based on Sony internal testing. Transfer speeds vary and are dependent on host devices, the OS version or usage conditions.

*When using with SBAC-US30 or SBAC-UT100, transfer speeds may be slower compared to conventional SxS cards. For high-speed data transfer, using with SBAC-T40 is recommended.

Stable 4K video capture of high bit rate

EB streaming technology, which enables constant two-way communication between cards and Sony camcorders, ensures a stable high frame rate recording, while avoiding speed degradation. Capable of recording up to 45 minutes of XAVC 4K 60p (600 Mbps) footage in a 240-GB card with compatible Sony camcorders, such as VENICE.

Proven Reliability for Professionals

Continuously verified through strict inspections and various quality-assurance tests on the manufacturing process as the best trusted professional memory cards.

Memory Media Utility

Sony's application software, Memory Media Utility, allows you to manage SxS memory cards with features such as the library function, remaining media lifetime/capacity indicator, simultaneous data back-up to three locations, and quick/full formatting.

Robustness and durability*

Passed a variety of stringent durability tests. Provides a high standard of reliability to meet the specific requirements of professional users, even under extreme shooting conditions.

*Performance test by Sony internal Standard.

Compatible Devices

When using SBP-240F/120F with the compatible devices listed below, you will need to update the device's system software to the version shown in parentheses or higher. For details, see the information on each device's website.

When using SBP-240F/120F with compatible card readers, you will need to install the latest version of the SxS Device Driver.

When using SBP-240F/120F with SBAC-US30 or SBAC-UT100, you need to update the device's system software via Memory Media Utility version 4.3.1 or later.

*Compatible Devices: PXW-X500 (V6.10), PXW-X400 (V4.10), PXW-Z450 (V4.10), MPC-3610 (V2.10), PMW-F55/F5 (V9.20) and PXW-Z280 (V1.20).

Interface	ExpressCard/PCI Express 3.0
Model Names	SBP-120F & SBP-240F
Capacity*1	120 GB (SBP-120F) 240 GB (SBP-240F)
Max. Read Speed*2	10 Gbps (1,250 MB/s)
Max. Write Speed*2	4.8 Gbps (600 MB/s)
Min. Write Speed*2	1.3 Gbps (162.5 MB/s)
Operating Temperature	-25°C~65°C
Storage Temperature	-40°C~85°C
Weight	Approx. 27g
Dimension (W x D x H)	1.34 x 0.20 x 2.95 in
Warranty	10 years
Software	Memory Media Utility
Note	<p>*1 A portion of the memory is used for system files and may vary.</p> <p>*2 Based on Sony internal testing. Transfer speeds vary and are dependent on host devices, the OS version or usage conditions.</p>

Related products



PXW-X400

Three 2/3-inch type Exmor CMOS sensors XDCAM weight-balanced advanced shoulder camcorder with HLG option, improved network connectivity, and low power consumption



PXW-Z280

World's first 4K Handheld Camcorder with 1/2-type 3CMOS with 4K 50p/60p recording capability, 12G-SDI, Dual Link Cellular capability, 17x zoom lens, advanced Face Detection AF



PXW-Z450

4K HDR 2/3-type CMOS sensor shoulder camcorder with advanced network features, low power consumption and optimized weight balance



VENICE

Next generation camera with forward thinking full frame sensor, phenomenal color science and user-friendly operation.



SBAC-T40

SxS memory card Thunderbolt 3 reader/writer



PXW-X500

Three 2/3-inch type PowerHAD FX Full HD CCD sensors XDCAM camcorder with multi-format recordings including XAVC



PMW-F5

Super 35mm 4K CMOS sensor compact CineAlta camera records HD/2K on SxS memory plus 16-bit RAW 2K/4K output



PMW-F55

Super 35mm 4K CMOS sensor compact CineAlta camera records HD/2K/4K on SxS memory plus 16-bit RAW 2K/4K output



PMW-F55LIVE

Super 35mm 4K CMOS sensor compact CineAlta camera records HD/2K/4K on SxS memory plus 16-bit RAW 2K/4K output

Gallery

