

SRG-A12

PTZ Auto Framing Camera with AI Analytics, 12x optical zoom, and NDI®|HX capability



Overview

A Camera that Automatically and Naturally Shoots Video for you

With the advanced PTZ Auto Framing feature, the camera automatically tracks the target in a comfortable viewing with smooth pan, tilt, zoom movement, regardless of posture, movement and what they are wearing. Since there is no need for a dedicated operator, this is a system cost advantage.

The SRG-A12 harnesses powerful AI-powered video analytics that can automatically detect and track the position of a presenter within the camera frame. As the presenter moves, the camera's pan/tilt/zoom mechanism ensures that the presenter is always framed accurately and naturally, without the need for a human camera operator to manually follow their movements.

Features

Automatic and reliable

With Sony's newly developed AI Analytics unit, it detects the subject's skeleton and tracks the subject, even when there are several people in the frame.

Choice of three shooting modes

The SRG-A12 has a choice of three shooting modes; Full body, Waist, and Close-up. In each mode, you can select the center, left, or right angle of view, and the SRG-A12 can automatically track

the subject in the selected optimal position.

Integrated tally lamp

The SRG-A12 features a built-in tally lamp, just like you'd find on professional studio cameras. The lamp illuminates to give presenters visual confirmation of shooting status, or to show that PTZ Auto Framing mode is active. The lamp color will change from Red (standby) to Green (PTZ Auto Framing ON).

High speed pan/tilt

Speedy, precise pan/tilt operation ensures that the camera can accurately keep track of the presenter's movements.

Wide angle zoom lens

As well as powerful close-ups, the SRG-A12 can capture broad shots of the presenter or audience with a wide field of view.

Clear Zoom

Digital plus optical zoom increases maximum magnification to a huge 24x for frame-filling close-ups without reducing resolution.

4K Exmor R sensor

The highly sensitive 1/2.5-type image sensor captures crisply-detailed 4K video with extremely low picture noise, even when shooting in low light.

IP streaming

Stream 4K 30p video from the camera with support for popular IP protocols – ideal for live events and webcasts.

PoE++ support

Support for next-generation Power over Ethernet simplifies installation, with camera power, control and IP video all carried by a single LAN cable.

HDMI/SDI outputs

As well as live streaming over IP, the camera can simultaneously

output video via HDMI and SDI for conventional production.

Picture Setting File

Easily copy picture settings across multiple cameras for quick, convenient set-up in multi-camera shooting environments.

Remote control of PTZ operation

Pan/Tilt/Zoom camera movements and other functions can all be precisely controlled using the supplied IR remote commander, for convenient wireless control of PTZ functions without needing additional equipment. It can also be controlled using the optional additional IP500 remote controller, just like professional broadcast cameras.

Convenient control from a PC or tablet

Camera functions can also be controlled remotely from a networked PC or tablet* using our intuitive app.

*Windows only

Easy ceiling mounting

The camera comes supplied with a mounting plate for convenient ceiling installation, if required.

Light, compact design

The camera's stylish, compact body fits unobtrusively into any environment.

Choice of color finishes

The SRG-A12 is available in a choice of black or white color finishes, to suit the needs of any application.

Specifications

Camera

Image Sensor

1/2.5 type ExmorR CMOS

Image Sensor (Number of Effective Pixels)	Approx. 8.5M pixels
Signal System	2160/29.97p, 25p, 23.98p 1080/59.94p, 50p, 29.97p, 25p, 23.98p 1080/59.94i, 50i 720/59.94p, 50p
4K Capability	Yes
Minimum Illumination (50IRE)	1.6 lux (1/30s 50IRE F2 high- sensitivity OFF)
Horizontal Resolution	1700 TV lines (Center) (4K) 1000 TV lines or higher (Center) (FHD)
Gain	Auto/Manual (0 to +48 dB) High Sensitivity On
Shutter Speed	1/1 to 1/10000 sec (59.94 Hz system) 1/1 to 1/10000 sec (23.98 Hz system) 1/1 to 1/10000 sec (50 Hz system)
Exposure Control	Auto/Manual/Priority AE (Shutter, Iris)

White Balance	Auto1/Auto2/One Push WB/Indoor/Outdoor/Manual
Zoom Capability	30x (4K with CIZ*1), 40x (HD with CIZ), Max. 80x (HD with CIZ and Tele Convert Mode)
Focusing System	Auto/Manual
Horizontal Viewing Angle	Approx. 70.0 degree (Wide)
Focal Length	f=4.4 mm (Wide) to 88.0 mm (Tele)
F-number	F2.0 to F3.8
Minimum Object Distance	80 mm (Wide) – 800 mm (Tele)
Pan/Tilt Angle	Pan: $\pm 170^\circ$ Tilt: $+90^\circ/-20^\circ$
Pan/Tilt Speed (Max.)	Pan: 300 degrees/sec Tilt: 126 degrees/sec
Pan/Tilt Speed	Pan: 1.1° to $101^\circ/s$ Tilt: 1.1° to $91^\circ/s$
Pan/Tilt Speed (Slow)	Pan: 0.5° to $60^\circ/s$ Tilt: 0.5° to $60^\circ/s$
Pan/Tilt Slow Mode	Yes

Pan/Tilt Operation Noise	NC30 or less *2
--------------------------	-----------------

Preset Position	256 (CGI) 100 (VISCA)
-----------------	--------------------------

Picture Freeze Preset	Yes
-----------------------	-----

PTZ Motion Sync	Yes
-----------------	-----

Network

IP Video Resolution	3840 x 2160, 1920 x 1080, 1280 x 720, 640 x 360
---------------------	--

Compression Format	H.264: High/Main/Baseline Profile H.265: Main Profile
--------------------	--

Maximum Frame Rate	H.264: 60fps H.265: 60fps
--------------------	------------------------------

Bitrate Compression Mode	CBR/VBR (selectable)
--------------------------	----------------------

Range of Bitrate Setting	512 kbps~50 Mbps
--------------------------	------------------

Multi-Streaming Capability	3
----------------------------	---

Maximum Number of Clients	5
---------------------------	---

Protocols	IPv4, IPv6, TCP, UDP, ARP, ICMP, HTTP, HTTPS, DHCP, DNS, RTP/RTCP, RTSP, VISCA over IP, SRT
-----------	---

NDI HX Capability	Yes Option (need to attach a license)
-------------------	--

Camera Features

Auto ICR (Auto mode of IR Cut filter Removal)	Yes
---	-----

Day/Night	Yes
-----------	-----

Visibility Enhancer	Yes
---------------------	-----

Image Stabilizer	Yes
------------------	-----

Image Flip	Yes
------------	-----

Picture Setting File	Yes
----------------------	-----

Flicker Cancel	On/Off
----------------	--------

Hide OSD Menu	On/Off
---------------	--------

Standby Mode	Yes
--------------	-----

Remote Standby	Yes
----------------	-----

PTZ Auto Framing	Yes
------------------	-----

Web UI

Version Up	Yes
Languages	Japanese, English, French, Spanish, German, Italian, Chinese, Traditional Chinese, Korean, Portuguese, Russian, Polish, Hindi, Turkish
OS and Browser	Windows 11 64-bit w/Chrome, Windows 10 64-bit w/Chrome, Windows 11 64-bit w/Edge, Windows 10 64-bit w/Edge, macOS 11 w/Chrome, macOS 12 w/Chrome, macOS 13 w/Chrome*3

Audio

Channel	2 ch
Audio Codec	AAC LC 128 kbps/ST (IP) AAC LC 256 kbps/ST (IP)
Setting Option	Auto level control: On/Off, Equalizer: Off/Low cut/Voice enhancement, Input selection: Microphone/Line,

Mic volume: -10~+10 (21 steps),
Audio codec

Embedded Audio in Baseband Video	Yes (3G-SDI, HDMI)
----------------------------------	--------------------

Embedded Audio in IP Streaming	Yes
--------------------------------	-----

Interface

4K Video Output	HDMI x1, IP (streaming) x1
-----------------	-------------------------------

HD Video Output	3G-SDI x1, HDMI x1, IP (streaming) x1
-----------------	---

SD Video Output	IP (streaming) x1
-----------------	-------------------

Remote Video Format Switching	Yes
-------------------------------	-----

HDMI Color Space	YCbCr, 4:2:2 8bit RGB, 4:4:4 8bit
------------------	--------------------------------------

Camera Control Interface	VISCA RS-422 RJ45 (In/Out) VISCA over IP RJ45
--------------------------	--

IR Remote Control	Yes
-------------------	-----

Microphone Input	Stereo Mini-phone (φ3.5 mm) x1,
------------------	---------------------------------

(Mic/Line Selectable)

Sync. System	INT
Tally	Front x 1 Red/Green (for PTZ Auto Framing)
Power Connector Type	IEC60130-10 (JEITA standard RC-5320A) Type5

General

Power Requirements	DC 19.5 V PoE++ (IEEE802.3bt type4 class8)
Power Consumption	DC19.5 V: 80W PoE++: 71.3W
Operating Temperature	0 °C to 40 °C 32 °F to 104 °F
Storage Temperature	-20 °C to +60 °C -4 °F to +140 °F
Dimensions (W x H x D)*4	156.7 x 184.0 x 200.0 mm 6 1/4 x 7 1/4 x 7 7/8 in
Mass	Approx. 2.0 kg (Approx. 4 lb 6.5 oz)
Body Color	White/Black

Size of Screw Hole for Tripod	1/4-20UNC x1
Mountable Angle	< $\pm 15^\circ$
Ceiling Mount	Yes
Accessories	AC power adaptor (1) IR Remote Commander Unit (1) Ceiling bracket (2) Wire rope (1) Screw M3 x 8 (9) Screw M2.6 x 6 BLACK (1) HDMI cable fixing plate (1) Safety regulation (1) Download site information (1) Warranty (1)

Notes

*1	CIZ = Clear Image Zoom
*2	Sony measurement conditions
*3	Available from V2.0 and later
*4	The values for dimensions are approximate

Gallery



