

ZRD-CH15D

Crystal LED video wall modular display cabinet with immersive image depth



Overview

Premium super-size images delivering an immersive sense of depth

The latest generation of Crystal LED premium displays from Sony makes the appeal of super-size LED video walls even more accessible.

The ZRD-CH15D delivers spectacularly bright, richly colored images in a wide range of environments – including corporate lobbies, entrances, boardrooms and retail showrooms – even in brightly-lit spaces.

Sony's unique surface treatment technology, Deep Black Coating and the huge black area in display by using super fine LED achieve outstanding black levels for truly immersive environments. This enables the ZRD-CH15D to achieve outstanding black levels that are superior to other high-end LED video walls. Coupled with the display's extra-wide color gamut, it ensures immersive images with a vivid sense of depth.

Advanced 4K 120Hz driver technology is augmented by real-time image enhancement features powered by Sony's X1 for Crystal LED picture processor. Every video frame is individually analyzed and optimized, ensuring content looks crisp and super-smooth, even if it wasn't originally shot for large-scale display.

The borderless design of each energy-efficient Crystal LED panel allows multiple ZRD-CH15D cabinets to be tiled seamlessly, creating super-size high resolution displays with virtually any dimensions or aspect ratio – and no bezels or visible gaps. Crystal LED also offers simplified integration compared with previous-generation systems, with slim, light panels that are easy to install and maintain without requiring special skills or complex equipment.

Features

Glare-free, immersive viewing with the deepest black levels

Sony's unique surface treatment technology, Deep Black Coating and the huge black area in display by using super fine led achieve outstanding black levels for truly immersive environments. The advanced anti-reflection coating reduces glare from ambient lighting, ensuring truly immersive images with bright, vibrant colors and deep black levels that bring more contrast, depth and texture to faces and other on-screen objects.

Extraordinary colors

True-to-life, smoothly graduated colors are a must-have for critical viewing applications. Advanced Sony LED driver technology enables an extra-wide color gamut. You'll see the difference with rich, vibrant colors, even in bright viewing conditions. The ZRD-CH15D reproduces color gradations with immense accuracy, using a 22-bit Super Bit Mapping process that's enabled by the X1 for Crystal LED picture processor. Audiences can see the difference with smooth, natural color transitions and faithful reproduction of subtle tones in dark scenes.

Uniform color at all viewing angles

Super fine LED and Sony's unique coating technology reduce color shifting when the display is viewed from any angle –

ensuring an immersive viewing experience for everyone in the room.

Spectacular results with lower resolution content

Lower-resolution content doesn't often look its best when it's displayed on a large LED screen, with images appearing grainy and pixilated. The ZRD-CH15D uses Reality Creation to upscale and optimize lower-quality content to near 4K resolution for crisp, natural big-screen viewing.

Smooth, fluid movement

Fast-moving action can be blurry and uncomfortable to watch on a big display. Motionflow inserts additional video frames to ensure smoother, sharper detail and a more natural viewing experience in fast-moving sequences.

Wide viewing angle and natural color

The ZRD-CH15D delivers a spectacularly immersive, totally seamless visual experience with an extra-wide viewing angle and no unnatural color shifts. Super fine LED and Sony's unique coating technology reduce color shifting when the display is viewed from any angle.

Seamless images with consistently accurate color

Display modules are factory preassembled and calibrated to ensure quick, precise installation. Color adjustment* is simplified with our easy-to-use auto adjustment tool using a Sony Alpha camera.

*Color adjustment available via future firmware update

Easy installation, minimal maintenance

The ZRD-CH15D offers simplified installation and maintenance compared with previous-generation LED wall systems. Newly designed cabinets are thin and light, broadening options for integration in spaces with limited depth or weight restrictions. With fewer parts to assemble, on-site installation time and costs are reduced. All system components and cabling are accessible

from the front, simplifying maintenance where there's no rear access.

Specifications

General	
Pixel Pitch	1.59 mm
Surface	Deep black coating
Resolution (W x H)	384 x 216
Brightness (max.)	1,300 cd/m ²
Contrast Ratio (0 lx)	More than 1,000,000:1
Viewing Angle (H/V)	160 °/160 °
Color Gamut	Approx. 86% (BT2020, Δu'v' coverage) Approx. 97% (DCI-P3, Δu'v' coverage) Approx. 148% (sRGB, Δu'v' area)
Bit Depth	22-bit Internal Processing
Frame Rate	Up to 120 frames per second
Signal Interface	1 in 1 out (2 x RJ45)
Operating Temperature / Operating Humidity	32 °F to 104 °F / 20% to 80% (no condensation)

Storage Temperature / Storage Humidity	-4 °F to 140 °F / 20% to 80% (no condensation)
Power Requirements	AC 100–240 V, 50/60 Hz
Power Consumption (Max.)*	At Max brightness: 120W (Per-sqm: 574W) At 800 cd/m ² : 84W (Per-sqm: 408W)
Power consumption (ave.)	55 W (Per sqm: 263 W)
Dimensions (W x H x D)	610 x 343 x 69 mm (24 1/8 × 13 5/8 × 2 3/4 in)
Mass	Approx. 8.6 kg (18 lb 15.36 oz) (Per-sqm: Approx. 41.1 kg)
Application	Indoor
Notes	Please refer to the installation manual for installation.

Related products



ZRD-CH12D

Crystal LED video wall modular display cabinet with immersive image depth



ZRCT-300

Display Controller for LED wall display cabinets



ZRD-BH15D

Crystal LED video wall modular display cabinet with high brightness and rich color



ZRD-BH12D

Crystal LED video wall modular display cabinet with high brightness and rich color

Gallery

